



NOTES:

1. ITEM: Hex Head Plug
2. MAX. PRESSURE: 300 psi
3. PIPE SIZE - PIPE FITTING: 1/4"
4. FITTING CONNECTION TYPE: MNPT
5. PIPE FITTING MATERIAL: 304 Stainless Steel
6. STANDARDS: Material Conforms To ASTM-A-351,
Threads Conform To ANSME B1.20.1,
Meets MSS-SP-114 Class 150 Pressure Ratings

COMPONENT	Stainless Steel Pipe Fitting
------------------	------------------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 3.33

<h1>1LTK5</h1> <p>Hex Head Plug, 1/4 In, Threaded, 304 SS</p>	UNIT
	INCH
	SHEET
	1 of 1