



**NOTES:**

1. COLOR : Gray
2. TUBE SIZE : 1/4
3. MAX. PRESSURE : 150 psi
4. BASIC FITTING SHAPE : Elbow
5. PIPE SIZE - PIPE FITTING : 1/4
6. TUBE FITTING MATERIAL : Acetal Copolymer
7. FITTING CONNECTION TYPE : Tube x Male BSPT
8. TEMP. RANGE : -14°F to 167°F for Air and 33°F to 140°F for Water
9. STANDARDS : NSF-61 For Drinking Water,  
NSF-51 For Food And FDA For Food And Beverage

<b>COMPONENT</b>	Swivel Elbow, 90°
------------------	-------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE** 1.57

<b>1WRZ1</b>
90 Swivel Elbow, 1/4 in. Tube, Gray, PK10

<b>UNIT</b>	INCH
<b>SHEET</b>	1 of 1