



NOTES:

1. MAX. RPM: 38000
2. LUBRICATION: Grease
3. TYPE: Double Sealed
4. ITEM: Radial Ball Bearing
5. STATIC LOAD CAPACITY: 140Lb.
6. TEMP. RANGE: -40°F to 350°F
7. DYNAMIC LOAD CAPACITY: 333Lb.
8. CAGE MATERIAL: Stamped Steel
9. SEAL MATERIAL: Nitrile Rubber
10. BEARING MATERIAL: Chrome Steel

GRAINGER

100 Grainger Parkway, Lake Forest, Illinois 60045-5201
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 4.28

COMPONENT	Radial Ball Bearing		
1ZGE6 Radial Bearing, DBL Seal, 0.2500 In. Bore	UNIT		
	INCH		
	SHEET		
	1 of 1		