



**NOTES:**

1. MATERIAL: Steel
2. MAX. RPM: 11000
3. TYPE: Double Sealed
4. LUBRICATION: MT47 Grease
5. ITEM: Radial Ball Bearing
6. STATIC LOAD CAPACITY: 4,300Lb.
7. SEAL MATERIAL: Synthetic Rubber
8. TEMP. RANGE: -40°F to 212°F
9. DYNAMIC LOAD CAPACITY: 7,300Lb.

|                  |                     |
|------------------|---------------------|
| <b>COMPONENT</b> | Radial Ball Bearing |
|------------------|---------------------|



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE**      0.94

**23Y233**

40 x 80 x 18 Radial Bearing, Double Seal,  
40mm Bore Dia

|              |        |
|--------------|--------|
| <b>UNIT</b>  | MM     |
| <b>SHEET</b> | 1 of 1 |