



NOTES:

1. INSERT: Alloy Steel
2. V-BELT SIZE RANGE: B
3. FORCE RANGE (Lb.): 0 - 42
4. TEMP. RANGE (°F): 32 - 225
5. IDLER OUTSIDE DIA.: 5.04"
6. MOUNTING HOLE (In.): 0.40"
7. APPLICATION: V-Belt Drives
8. TENSIONING ARM: Deflects Up to 30 Degrees Either Side of its Neutral Position

COMPONENT		Self-Adjusting Tensioner	
<h1>2ZRT9</h1>		UNIT	
		INCH	
Self-Adjusting Tensioner, B V-belt Size		SHEET	
		1 of 1	

GRAINGER
 100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE	0.44
--------------	------