



Series	Parker ST Series	Max. Pressure	2200 psi
Connection Type	MNPT	Quick Coupler Type	Hydraulic Coupler Nipple
Coupler Flow Rate	12.0 gpm	Locking Mechanism	Ball
Coupler Body Size	1/2"	Coupler Body Material	Brass
Coupler Thread Size	1/2"-14	Operating Temp. Range	-40° to 250°F

NOTES:

1. COUPLER FINISH: Plain
2. ITEM: Hydraulic Coupler Nipple
3. FOR USE WITH: Parker ST Series
4. PARKER INTERCHANGE: BST-N4M
5. BEARING MATERIAL: Stainless Steel
6. COUPLER INTERCHANGE TYPE: ST

COMPONENT	Hydraulic Quick Couplers
------------------	--------------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 1.60

31A983	UNIT
	INCH
	SHEET
	1 of 1

Coupler Nipple, 1/2-14, 1/2 In. Body, Brass