



NOTES:

1. ITEM : Heavy-Duty Long-Swivel-Life Bolt-Hole Caster
2. CASTER SUB-TYPE : Swivel
3. LOAD RATING : 1320 lb.
4. WHEEL/TREAD HARDNESS RATING : Hard
5. WHEEL/TREAD HARDNESS : 92-97 Shore A
6. WHEEL/TREAD COLOR : Gray
7. CASTER BRAKE TYPE : No Brake Included
8. CASTER FRAME MATERIAL : Steel
9. FRAME FINISH : Zinc Plated
10. WHEEL CORE MATERIAL : Iron
11. OPERATING TEMPERATURE RANGE : -22° to 176°F
12. APPLICATION : Material Handling
13. FEATURES : Different Stem Lengths, Hollow
14. STANDARDS : ICWM

COMPONENT		Bolt Hole Casters	
<h1>32MZ48</h1>		UNIT	INCH
		SHEET	1 of 1
SCALE		0.26	
HVY-Duty Long-SWVL-Life Bolt-Hole Caster			



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.