



NOTES:

1. MAX. RPM: 19000
2. ABEC TOLERANCE: 1
3. CAGE MATERIAL: Polyamide
4. TYPE: Double Row
5. TEMP. RANGE: -40°F to 350°F
6. LUBRICATION: Polyrex EM Grease
7. SEAL MATERIAL: Nitrile Rubber
8. ITEM: Angular Contact Ball Bearing
9. STATIC LOAD CAPACITY: 850Lb
10. DYNAMIC LOAD CAPACITY: 1600Lb / 7117.154592N

COMPONENT		Angular Contact Ball Bearing	
<h1>35HY94</h1>		UNIT	MM
		SHEET	1 of 1
		Angular Contact Ball Bearing, 850lb., NBR	



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 2.50