



NOTES:

1. SERIES: UCP
2. FINISH: Painted
3. NUMBER OF BOLTS: 2
4. STANDARDS: ISO, AFBMA
5. BEARING INSERT TYPE: Ball
6. TEMP. RANGE: -40 °F to 250 °F
7. SHAFT LOCKING TYPE: Set Screw
8. LOAD CAPACITY: Static - 1494 Lb. / Dynamic - 2877 Lb.
9. BEARING LUBRICATION: Shell Alvania RL2 or NLGI #2 Equivalent
10. BEARING MATERIAL: Housing - Cast Iron / Insert - 52100 Chrome Steel

COMPONENT	Pillow Block Bearing	
36UY98	Pillow Block Bearing, Ball, 1/2" Bore	
	UNIT	MM
	SHEET	1 of 1
	SCALE	0.86



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.86