



NOTES:

1. ITEM : General Purpose Bolt-Hole Caster
2. CASTER SUB-TYPE : Swivel
3. LOAD RATING : 440 lb.
4. WHEEL/TREAD HARDNESS RATING : Soft
5. WHEEL/TREAD HARDNESS : 70 Shore A
6. WHEEL/TREAD COLOR : Black
7. CASTER BRAKE TYPE : No Brake Included
8. CASTER FRAME MATERIAL : Steel
9. FRAME FINISH : Zinc Plated
10. WHEEL CORE MATERIAL : Nylon
11. OPERATING TEMPERATURE RANGE : -40° to 158°F
12. APPLICATION : Tool and Work Boxes
13. FEATURES : Kingpin Less Press Steel, Hallow
14. STANDARDS : ICWM

COMPONENT		Bolt Hole Casters	
<h1>38LU26</h1>		UNIT	INCH
		SHEET	1 of 1
General Purpose Bolt-Hole Caster, 5"		SCALE	0.39



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.