



NOTES:

1. STANDARDS : ICWM
2. CORE COLOR : Gray
3. LOAD RATING : 175 lb.
4. CASTER SUB-TYPE : Swivel
5. WHEEL/TREAD COLOR : Gray
6. FRAME FINISH : Zinc Plated
7. CASTER FRAME MATERIAL : Steel
8. WHEEL/TREAD MATERIAL : Neoprene
9. CASTER STEM TYPE : Hollow Kingpin
10. WHEEL/TREAD HARDNESS : 90 Shore A
11. WHEEL/TREAD HARDNESS RATING : Firm
12. CASTER BRAKE TYPE : Side Thumbscrew Brake
13. OPERATING TEMPERATURE RANGE : -30° to 175°F
14. ITEM : Low-Profile Easy-Turn Bolt-Hole Caster

| | |
|------------------|-------------------|
| COMPONENT | Bolt Hole Casters |
|------------------|-------------------|

GRAINGER
 100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.77

454Y34

Low-Profile Easy-Turn Bolt-Hole Caster

| | |
|--------------|--------|
| UNIT | INCH |
| SHEET | 1 of 1 |