





4.8 [0.19]
Hollow Hex.



NOTES:

1. ITEM: Cartridge Valve
2. VALVE CAVITY SIZE: C10-3
3. CARTRIDGE VALVE ITEM: Cartridge Valve
4. MAX. FLOW - HYDRAULIC VALVES: 12.0 gpm
5. CARTRIDGE VALVE TYPE: Counterbalance
6. MAX. PRESSURE - HYDRAULIC VALVES: 5000 psi
7. APPLICATION: Used to Control Overrunning Loads in Systems with Varying Loads or Varying Speeds

COMPONENT		Hydraulic Cartridge Valves	
<h1>4DMK4</h1>		UNIT	
		MM (INCH)	
Cartridge Valve, Counterbalance, 12 GPM		SHEET	
			1 of 1



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.82