


Item	Hydraulic Gear Pump	Mounting	SAE A 2 Bolt
Housing	Aluminum	Ports (Inlet)	1-1/16-12
Rotation	R	Ports (Outlet)	7/8-14
Max. RPM	3000	Cover Material	Cast iron
Min. RPM	500	Shaft Extension (In.)	3/4 x 1-1/4 Keyed



NOTES:

1. NOMINAL GPM @ 1200 RPM: 5.1
2. GPM @ 1800 RPM & 1000 PSI: 7.1
3. MAX. CONTINUOUS PSI: 4000
4. DISPLACEMENT (CU. IN./REV.): 0.98
5. DESIGN: Pressure-balanced, With 90 Percentage Overall Efficiency and Low Noise

COMPONENT	Hydraulic Gear Pumps
-----------	----------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.30

4F669

Pump, Hydraulic Gear

UNIT	MM (INCH)
SHEET	1 of 1