



#### NOTES:

1. HEAD TYPE : Round
2. MATERIAL : Grade 5 Medium Carbon Steel
3. FINISH : Chrome
4. NECK TYPE : Square
5. TENSILE STRENGTH (PSI) : 120,000
6. DRILL SIZE : 21/64"
7. FOR USE WITH : Grade 2 Nuts
8. MEETS/EXCEEDS : ASME B18.5

COMPONENT	Carriage Bolt		
<b>4GVC5</b>  Bolt, Carriage, Chr, 5/16-18 x 2, PK5	UNIT		
	INCH		
	SHEET		
	1 of 1		

**GRAINGER**

100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
[www.grainger.com](http://www.grainger.com)

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 2.06