



NOTES:

1. DUTY: Continuous
2. FORCE: Sinusoidal
3. INLET PORT: 3/8 NPT
4. GPM @ 1000 PSI: 6.5
5. OUTLET PORT: 3/8 NPT
6. MAX. PRESSURE: 3000 psi
7. FORCE @ 1000 psi: 488 Lb.
8. SPEED @ 1000 psi: 7400 VPM
9. VIBRATOR TYPE: Low Frequency
10. BIN WEIGHT CAPACITY: 3320 Lb.
11. MOUNTING PLATE: Sold Separately

COMPONENT		Hydraulic Vibrator	
4HT14 Vibrator, Hydraulic		UNIT	INCH
		SHEET	1 of 1
SCALE	0.550		



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.