



NOTES:

1. HANDLE: No
2. BODY MATERIAL: Steel
3. ITEM: Hydraulic Cylinder
4. WEIGHT CAPACITY: 100 tons
5. MAX. PRESSURE: 10,000 psi
6. CYLINDER TYPE: Low Height
6. INCLUDES: Female Coupler, Dust Cap
8. SINGLE ACTING/DOUBLE ACTING: Single Acting

COMPONENT	High Pressure Hydraulic Cylinders
------------------	-----------------------------------

GRAINGER
 100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE	0.31
--------------	------

4PU63

Cylinder, 100 tons, 2-1/4in. Stroke L

UNIT	MM
SHEET	1 of 1