



Ø7/16 SUPPORT HOLES

MOUNTING DETAILS



NOTES:

1. FRAME SHAPE : Straight
2. FRAME MATERIAL : Steel
3. CONVEYOR FRAME TYPE : Rigid
4. ROLLER BEARING TYPE : Ball Bearing
5. CONVEYOR ROLLER MATERIAL : Steel
6. LOAD CAPACITY @ 5 FT. CENTERS : 600 lb./ft.
7. LOAD CAPACITY @ 10 FT. CENTERS : 120 lb./ft.
8. MAXIMUM LOAD CAPACITY : 600 lb./ft. (5 ft. Supports)
9. FRAME FINISH/COATING : Powder Coated

COMPONENT		Roller Conveyor	
4W577		UNIT	INCH
		SHEET	1 of 1
Roller Conveyor, 10 ft. L, 22" BF, Steel			



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.09