



NOTES:

1. FINISH: Rustproof Plated
2. ITEM: 2-Bolt Flange Bearing
3. SHAFT LOCKING TYPE: None
4. TEMP. RANGE: -5°F to 220°F
5. BEARING INSERT TYPE: Sleeve
6. BEARING INSERT MATERIAL: Bronze
7. DYNAMIC LOAD CAPACITY: Max. PV 50,000Lb.
8. BEARING LUBRICATION: 20 Weight Non-Detergent Oil
9. BEARING HOUSING MATERIAL TYPE: Pressed Steel

COMPONENT	2-Bolt Flange Bearing
------------------	-----------------------



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.69

4X815 Flange Bearing, 2-Bolt, Sleeve, 1/2" Bore	UNIT
	INCH
	SHEET
	1 of 1