



NOTES:

1. MAX. RPM: 11,000
2. ABEC TOLERANCE: 1
3. CONTACT ANGLE: 40°
4. CAGE MATERIAL: Pressed Steel
5. TEMP. RANGE: -13°F to 250°F
6. CAGE MATERIAL: Pressed Steel
7. ITEM: Angular Contact Ball Bearing
8. STATIC LOAD CAPACITY: 3050Lb / 13567N
9. DYNAMIC LOAD CAPACITY: 4600Lb / 20462N

COMPONENT		Angular Contact Ball Bearing	
<h1>4ZXZ1</h1> <p>Angular Bearing, 40 Deg, 30mm Bore, 62mm OD</p>		UNIT	MM
		SHEET	1 of 1
		SCALE	1.21



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.