



**NOTES:**

1. MAX. FLOW: 250 cfm
2. ITEM: Quick Coupler Body
3. FINISH: Trivalent Chrome
4. TEMP. RANGE: -40° to 250°F
5. APPLICATION: On End of Hose or Pipe, Water or Air
6. PIPE SIZE - QUICK CONNECT AIR COUPLINGS: 3/8"
7. BODY SIZE - QUICK CONNECT AIR COUPLINGS: 1/2"
8. SEALS - QUICK CONNECT AIR COUPLINGS: Buna-N
9. MATERIAL - QUICK CONNECT AIR COUPLINGS: Steel
10. MAX. PRESSURE - QUICK CONNECT AIR COUPLINGS: 300 psi
11. INTERCHANGE TYPE - QUICK CONNECT AIR COUPLINGS: Thor
12. LOCKING TYPE - QUICK CONNECT AIR COUPLINGS: Push-to-Connect
13. HOSE CONNECTION - QUICK CONNECT AIR COUPLINGS: (M)NPT

<b>COMPONENT</b>		Quick Connect Air Coupling	
<b>5CGP6</b>		<b>UNIT</b>	
		INCH	
Male to Thor Coupler,(M)NPT,1/2,Steel		<b>SHEET</b>	
		1 of 1	



100 Grainger Parkway, Lake Forest, Illinois 60045-5201  
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000  
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

**SCALE** 1.28