



NOTES:

1. MAX. FLOW: 26 cfm
2. ITEM: Quick Coupler Plug
3. FINISH: Trivalent Chrome
4. TEMP. RANGE: -40° to 250°F
5. APPLICATION: On End of Hose or Pipe
6. BARB SIZE - QUICK CONNECT AIR COUPLINGS: 1/4"
7. BODY SIZE - QUICK CONNECT AIR COUPLINGS: 1/4"
8. SEALS - QUICK CONNECT AIR COUPLINGS: Buna-N
9. MATERIAL - QUICK CONNECT AIR COUPLINGS: Steel
10. MAX. PRESSURE - QUICK CONNECT AIR COUPLINGS: 500 psi
11. HOSE CONNECTION - QUICK CONNECT AIR COUPLINGS: Hose Barb
12. INTERCHANGE TYPE - QUICK CONNECT AIR COUPLINGS: Tru-Flate-Automotive

COMPONENT		Quick Connect Air Coupling	
5CGY8		UNIT	
		INCH	
Barb to Automotive Plug, Barb, 1/4, Steel		SHEET	
		1 of 1	



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 2.35