



NOTES:

1. NUMBER OF BOLTS: 2
2. BEARING INSERT TYPE: Ball
3. TEMP. RANGE: -4 °F to 230 °F
4. SHAFT LOCKING TYPE: Set Screw
5. SERIES: Corrosion Resistant with USDA-H1 Grease
6. LOAD CAPACITY: Static - 1420 Lb. / Dynamic - 2680 Lb.
7. BEARING MATERIAL: Housing - PBT / Insert - 52100 Chrome Steel
8. BEARING LUBRICATION: Caltex FM EP or Equivalent USDA-H1 Grease

COMPONENT		Pillow Block Bearing	
5ZMX5		UNIT	INCH
		SHEET	1 of 1
Pillow Block Bearing, Ball, 1" Bore		SCALE	0.662



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 0.662