



NOTES:

1. FINISH: Painted
2. SERIES: Standard Duty
3. NUMBER OF BOLTS: 2
4. BEARING INSERT TYPE: Ball
5. TEMP. RANGE: -20 °F to 250 °F
6. SHAFT LOCKING TYPE: Set Screw
7. LOAD CAPACITY: Static - 2540 Lb. / Dynamic - 4400 Lb.
8. BEARING LUBRICATION: Shell Alvania #3 or NLGI #3 Equivalent
9. BEARING MATERIAL: Housing - Cast Iron / Insert - 52100 Chrome Steel

COMPONENT		Pillow Block Bearing	
5ZUG4		UNIT	INCH
		SHEET	1 of 1
Pillow Block Bearing, Ball, 1-1/4" Bore		SCALE	0.62



100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.