



NOTES:

1. TUBE SIZE : 3/16
2. FLARE TYPE : Inverted
3. STANDARDS : SAE J512
4. MAX. PRESSURE : 1900 psi
5. BASIC FITTING SHAPE : Tee
6. TEMP. RANGE : -65° to 250°F
7. TUBE FITTING MATERIAL : Brass
8. SPECIFIC FITTING SHAPE : Tee Union

COMPONENT	Union Tee
------------------	-----------

GRAINGER
 100 Grainger Parkway, Lake Forest, Illinois 60045-5201
 1-(800) GRAINGER, 1-(800) 472-4643, (847) 535-1000
 www.grainger.com

This file and any associated information and specifications are provided for reference and evaluation purposes only, and is subject to change without notice. Grainger makes no representations, warranties or guarantees as to the appropriateness, accuracy, completeness, or suitability for any purpose, of the file, information or specifications. You are solely responsible for the use of the file, information or specifications.

This drawing is the property of GRAINGER. It contains confidential, proprietary information that is GRAINGER property. Do not disclose to or duplicate for others except as authorized by GRAINGER.

SCALE 3.18

6JLG2

Union Tee, Inverted, 3/16 In., PK10

UNIT	INCH
SHEET	1 of 1