

# TRANSFER PIPETS

Includes 52 **NEW** sterile pipets!

Designed for the safe and convenient transfer of liquids.

## Globe Scientific Transfer Pipets

Globe Scientific offers the most extensive line of plastic transfer pipets for liquid handling procedures. Produced from a custom grade of low-density polyethylene (LDPE), these unbreakable one-piece pipets are used to draw and dispense liquids in controlled, reproducible drop sizes.

Plastic transfer pipets are the perfect substitute for breakable glass Pasteur pipets, which can be a danger to laboratory personnel. And, because they are completely disposable, there is never any cross-contamination which is associated with reusable rubber bulbs.

An extensive selection of capacities, lengths and tip styles are offered to accommodate different industry needs. For blood collection, Globe Scientific offers a line of blood bank pipets which feature a specially designed stem to fit into blood collection tubes. For diagnostic kits and small volume requirements, mini transfer pipets are the ideal choice. Choose fine tip pipets for research applications and for transferring liquids into small vessels such as multi-well plates. From mini to jumbo, standard to specialty, sterile and non-sterile, Globe Scientific offers a plastic transfer pipet to suit your needs.

New sizes, styles and packaging are frequently added to our line. Check the latest product offerings at: [www.globescientific.com](http://www.globescientific.com) or call our technical sales department for assistance at (201) 599-1400.

### Features

- Non-toxic and chemically inert to biological fluids and most acids.
- Can be heat sealed to use for liquid storage or transport.
- Pipets can be frozen in liquid nitrogen.
- Produced from a custom grade of low-density polyethylene (LDPE) to make them non-slippery. This makes Globe Scientific pipets easy to grip with gloves.
- Custom packaging is available. Please inquire.

### Technical Information

- Temperature range: -50°C to 90°C
- Can be gas (EtO) sterilized

### Non-Sterile Packaging



*Dispenser box, non-sterile*

Globe Scientific's non-sterile transfer pipets are packaged in a unique dispenser box. This convenient box is small and compact and ideal for bench-top use. The hinged front panel opens for quick access to the pipets and can be closed when not in use to keep the contents clean. *Exceptions: The exact volume pipets (page 3) are packaged in bags of 500, 10 bags per case, and the bellows pipets (page 10) are packaged in bags of 100, 12 or 20 bags per case.*

### Sterile Packaging



*Individually-wrapped (1/pack), sterile*



*10 pieces per bag  
(10/pack), sterile*













*20 pieces per bag  
(20/pack), sterile*



Watch the video!

# Transfer Pipet Styles



Page

## Exact Volume

3

Designed to dispense in precise volumes, these accurate and economical pipets are available in 5 sizes.

## Non-Graduated

4

These popular non-graduated pipets are offered in a variety of styles.

## Graduated

5-6

Designed for measurements, these pipets feature molded-in graduation marks that will never fade or wash off.

## Blood Bank

7

Features specially designed stems to fit into blood collection tubes.

## Narrow Stem

8

The long, thin stems are flexible and can be bent to access narrow openings and small diameter tubes.

## Fine Tip

9

Ideal for dispensing small volumes, loading hemocytometers and transferring liquid to and from multi-well plates.

## Bellows

10

The accordion-shaped, high capacity bulb of the bellows pipet acts as a reservoir for filling and expelling liquids. The bulb provides strong suction for use with viscous liquids.

## Extra Long

10

Available in 9" and 12" lengths, these pipets are ideal for reaching into large bottles, 24-hour urine containers, jars and cylinders.

## Paddle Pipets

11

These dual-purpose pipets are used for small volume transfers and feature an integrated rigid paddle used for mixing, spreading and smearing.

## Mini

12

Most popular size for use in diagnostic test kits and where small volume samples are required.

## Wide Bore

Back Cover

Designed for the rapid and effective transfer of viscous liquids and small particulates.

## Exact Volume Transfer Pipets

**Easy to use, economical and accurate!**

These **exact volume transfer pipets** are produced from chemically resistant, low density polyethylene and are designed to dispense precise volumes. They are available in the 5 popular sizes shown below. Exact volume pipets are packaged 500 pipets per bag.

### Exact Volume

Actual Size

#### 50 $\mu\text{L}$ (0.05 mL) capacity



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139110	Non-sterile	500 pcs/bag, 10 bags/case	5000	<ul style="list-style-type: none"> <li>Capacity: 50 <math>\mu\text{L}</math></li> <li>Bulb draw: 50 <math>\mu\text{L}</math></li> <li>Total length: 59 mm (2.3")</li> <li>Stem diameter: 2.2 mm (0.1")</li> </ul>

#### 75 $\mu\text{L}$ (0.075 mL) capacity



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139112	Non-sterile	500 pcs/bag, 10 bags/case	5000	<ul style="list-style-type: none"> <li>Capacity: 75 <math>\mu\text{L}</math></li> <li>Bulb draw: 75 <math>\mu\text{L}</math></li> <li>Total length: 75 mm (3")</li> <li>Stem diameter: 2.2 mm (0.1")</li> </ul>

#### 100 $\mu\text{L}$ (0.10 mL) capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139114	Non-sterile	500 pcs/bag, 10 bags/case	5000	<ul style="list-style-type: none"> <li>Capacity: 100 <math>\mu\text{L}</math></li> <li>Bulb draw: 100 <math>\mu\text{L}</math></li> <li>Total length: 83 mm (3.3")</li> <li>Stem diameter: 2.3 mm (0.1")</li> </ul>

#### 200 $\mu\text{L}$ (0.20 mL) capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139116	Non-sterile	500 pcs/bag, 10 bags/case	5000	<ul style="list-style-type: none"> <li>Capacity: 200 <math>\mu\text{L}</math></li> <li>Bulb draw: 200 <math>\mu\text{L}</math></li> <li>Total length: 115 mm (4.5")</li> <li>Stem diameter: 2.5 mm (0.11")</li> </ul>

#### 250 $\mu\text{L}$ (0.25 mL) capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139118	Non-sterile	500 pcs/bag, 10 bags/case	5000	<ul style="list-style-type: none"> <li>Capacity: 250 <math>\mu\text{L}</math></li> <li>Bulb draw: 250 <math>\mu\text{L}</math></li> <li>Total length: 104 mm (4.1")</li> <li>Stem diameter: 2.8 mm (0.11")</li> </ul>

## 1.7 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138020B	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 1.7 mL</li> <li>Total length: 87 mm (3.4")</li> <li>Drops/mL: 25</li> <li>Stem diameter: 4.5 mm (0.18")</li> <li>Bulb draw: 0.9 mL</li> <li>Tip diameter: 2.4 mm (0.09")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138020-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
138020-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

## 4 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138060	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 4 mL</li> <li>Total length: 130 mm (5.1")</li> <li>Drops/mL: 25</li> <li>Stem diameter: 6.6 mm (0.26")</li> <li>Bulb draw: 2 mL</li> <li>Tip diameter: 2.5 mm (0.1")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138060-S01 <b>NEW!</b>	Sterile	100 pcs/bag, 4 bags/case	400	
138060-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 20 bags/case	400	

## 5 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138050	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Drops/mL: 23</li> <li>Stem diameter: 6.8 mm (0.27")</li> <li>Bulb draw: 2 mL</li> <li>Tip diameter: 2.4 mm (0.09")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138050-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
138050-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

## 7 mL capacity – standard




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138080	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 7 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Drops/mL: 20</li> <li>Stem diameter: 7.8 mm (0.31")</li> <li>Bulb draw: 3.2 mL</li> <li>Tip diameter: 3.1 mm (0.12")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138080-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
138080-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

## 8 mL capacity – large bulb



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138030	Non-sterile	400 pcs/dispenser box, 10 boxes/case	4000	<ul style="list-style-type: none"> <li>Capacity: 8 mL</li> <li>Total length: 152 mm (6.0")</li> <li>Drops/mL: 20</li> <li>Stem diameter: 6.2 mm (0.24")</li> <li>Bulb draw: 4.6 mL</li> <li>Tip diameter: 3 mm (0.12")</li> </ul>
	Non-sterile	400 pcs/dispenser box	400	
138030-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	
138030-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 20 bags/case	400	

## 8.5 mL capacity – large opening




← Large opening for viscous liquids

Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138090	Non-sterile	250 pcs/dispenser box, 10 boxes/case	2500	<ul style="list-style-type: none"> <li>Capacity: 8.5 mL</li> <li>Total length: 137 mm (5.4")</li> <li>Drops/mL: 18</li> <li>Stem diameter: 6.1 mm (0.24")</li> <li>Bulb draw: 4.9 mL</li> <li>Tip diameter: 4 mm (0.16")</li> </ul>
	Non-sterile	250 pcs/dispenser box	250	
138090-S01 <b>NEW!</b>	Sterile	Individually wrapped, 25 pcs/bag, 10 bags/case	250	



1.5 mL capacity – graduated to 0.3 mL – pediatric




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
136036	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 1.5 mL</li> <li>Total length: 116 mm (4.6")</li> <li>Drops/mL: 21</li> <li>Stem diameter: 3.2 mm (0.13")</li> <li>Bulb draw: 0.9 mL</li> <li>Tip diameter: 3.2 mm (0.13")</li> <li>Graduated up to: 0.3 mL</li> <li>Graduation increments: 0.1 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
136036-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
136036-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

3 mL capacity – graduated to 1 mL – small bulb




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
137035	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 3 mL</li> <li>Total length: 140 mm (5.5")</li> <li>Drops/mL: 25</li> <li>Stem diameter: 4.4 mm (0.17")</li> <li>Bulb draw: 2.2 mL</li> <li>Tip diameter: 2.4 mm (0.09")</li> <li>Graduated up to: 1 mL</li> <li>Graduation increments: 0.25 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
137035-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 20 bags/case	400	
137135	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	

5 mL capacity – graduated to 1 mL – large bulb




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
137030	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Total length: 145 mm (5.7")</li> <li>Drops/mL: 24</li> <li>Stem diameter: 4.8 mm (0.19")</li> <li>Bulb draw: 3.4 mL</li> <li>Tip diameter: 2.7 mm (0.11")</li> <li>Graduated up to: 1 mL</li> <li>Graduation increments: 0.25 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
137038	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	
137138	Sterile	10 pcs/pack, 10 packs/bag, 4 bags/case	400	
137238	Sterile	20 pcs/pack, 20 packs/case	400	

5 mL capacity – graduated to 1 mL – large bulb




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
137010	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Total length: 148 mm (5.8")</li> <li>Drops/mL: 25</li> <li>Stem diameter: 4.8 mm (0.19")</li> <li>Bulb draw: 3.4 mL</li> <li>Tip diameter: 2.7 mm (0.11")</li> <li>Graduated up to: 1 mL</li> <li>Graduation increments: 0.25 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
137018	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	
137010-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 20 bags/case	400	

5 mL capacity – graduated to 2.25 mL



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138070	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Total length: 150 mm (5.9")</li> <li>Drops/mL: 21</li> <li>Stem diameter: 7.2 mm (0.28")</li> <li>Bulb draw: 1.8 mL</li> <li>Tip diameter: 3 mm (0.12")</li> <li>Graduated up to: 2.25 mL</li> <li>Graduation increments: 0.25 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	

5 mL capacity – graduated to 2 mL




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
137040	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Drops/mL: 23</li> <li>Bulb draw: 1.8 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Stem diameter: 6.5 mm (0.25")</li> <li>Tip diameter: 2.8 mm (0.11")</li> <li>Graduated up to: 2 mL</li> <li>Graduation increments: 0.5 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
137040-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
137040-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

5 mL capacity – graduated to 2 mL




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
137050	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Drops/mL: 23</li> <li>Bulb draw: 2 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Stem diameter: 6.8 mm (0.27")</li> <li>Tip diameter: 2.6 mm (0.1")</li> <li>Graduated up to: 2 mL</li> <li>Graduation increments: 0.5 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	

7 mL capacity – graduated to 3 mL – large bulb




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
135030	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 7 mL</li> <li>Drops/mL: 20</li> <li>Bulb draw: 3.2 mL</li> <li>Total length: 160 mm (6.3")</li> <li>Stem diameter: 7.9 mm (0.31")</li> <li>Tip diameter: 3 mm (0.12")</li> <li>Graduated up to: 3 mL</li> <li>Graduation increments: 0.5 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
135038	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	
135138	Sterile	10 pcs/pack, 10 packs/bag, 4 bags/case	400	
135238	Sterile	20 pcs/pack, 20 packs/case	400	

7.5 mL capacity – graduated to 3 mL – large bulb




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
135010	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 7.5 mL</li> <li>Drops/mL: 21</li> <li>Bulb draw: 3.5 mL</li> <li>Total length: 148 mm (5.8")</li> <li>Stem diameter: 7.5 mm (0.30")</li> <li>Tip diameter: 3.2 mm (0.13")</li> <li>Graduated up to: 3 mL</li> <li>Graduation increments: 0.5 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
135010-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	

## 4 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138060	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 4 mL</li> <li>Drops/mL: 25</li> <li>Bulb draw: 2 mL</li> <li>Total length: 130 mm (5.1")</li> <li>Stem diameter: 6.6 mm (0.26")</li> <li>Tip diameter: 2.5 mm (0.1")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138060-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	
138060-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 20 bags/case	400	

## 5 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138050	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Drops/mL: 23</li> <li>Bulb draw: 2 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Stem diameter: 6.8 mm (0.27")</li> <li>Tip diameter: 2.4 mm (0.09")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138050-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
138050-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

## 5 mL capacity – 6 inch – graduated to 2 mL



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
137040	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Drops/mL: 23</li> <li>Bulb draw: 1.8 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Stem diameter: 6.5 mm (0.25")</li> <li>Tip diameter: 2.8 mm (0.11")</li> <li>Graduated up to: 2 mL</li> <li>Graduation increments: 0.5 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
137040-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
137040-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	


## 5 mL capacity – graduated to 2 mL



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
137050	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Drops/mL: 23</li> <li>Bulb draw: 2 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Stem diameter: 6.8 mm (0.27")</li> <li>Tip diameter: 2.6 mm (0.1")</li> <li>Graduated up to: 2 mL</li> <li>Graduation increments: 0.5 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	




## 1.2 mL capacity – short stem




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138040	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 1.2 mL</li> <li>Total length: 65 mm (2.56")</li> <li>Drops/mL: 25</li> <li>Stem diameter: 2.5 mm (0.1")</li> <li>Bulb draw: 0.9 mL</li> <li>Tip diameter: 2.5 mm (0.1")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138040-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
138040-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

## 4 mL capacity – short stem – large bulb




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
136020	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 4 mL</li> <li>Total length: 85 mm (3.4")</li> <li>Drops/mL: 24</li> <li>Stem diameter: 2.5 mm (0.1")</li> <li>Bulb draw: 3 mL</li> <li>Tip diameter: 2.5 mm (0.1")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
136020-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
136020-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

## 4.5 mL capacity – standard



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
136030	Non-sterile	500 pcs/dispenser box, 10 boxes/cases	5000	<ul style="list-style-type: none"> <li>Capacity: 4.5 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Drops/mL: 25</li> <li>Stem diameter: 2.5 mm (0.1")</li> <li>Bulb draw: 3.2 mL</li> <li>Tip diameter: 2.5 mm (0.1")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
136030-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
136030-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	


## 6.5 mL capacity



Designed for use with spectrophotometer cuvettes


Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139020	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 6.5 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Drops/mL: 28</li> <li>Stem diameter: 7.8 mm (0.31")</li> <li>Bulb draw: 3.2 mL</li> <li>Tip diameter: 2.1 mm (0.08")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	

## 15 mL capacity – large bulb



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139040	Non-sterile	250 pcs/dispenser box, 10 boxes/case	2500	<ul style="list-style-type: none"> <li>Capacity: 15 mL</li> <li>Total length: 155 mm (6.1")</li> <li>Drops/mL: 19</li> <li>Stem diameter: 3 mm (0.12")</li> <li>Bulb draw: 8 mL</li> <li>Tip diameter: 3 mm (0.12")</li> </ul>
	Non-sterile	250 pcs/dispenser box	250	
139040-S01 <b>NEW!</b>	Sterile	Individually wrapped, 25 pcs/bag, 10 bags/case	250	
139040-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 25 bags/case	500	

1.3 mL capacity – small




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
134010	Non-sterile	500 pcs/dispenser box, 8 boxes/case	4000	<ul style="list-style-type: none"> <li>Capacity: 1.3 mL</li> <li>Total length: 51 mm (2.0")</li> <li>Drops/mL: 45</li> <li>Stem diameter: 1.15 mm (0.05")</li> <li>Bulb draw: 1 mL</li> <li>Tip diameter: 1.15 mm (0.05")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	

1.5 mL capacity – extended tip – small bulb




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
134020	Non-sterile	400 pcs/dispenser box, 8 boxes/case	3200	<ul style="list-style-type: none"> <li>Capacity: 1.5 mL</li> <li>Total length: 104 mm (4.1")</li> <li>Drops/mL: 50</li> <li>Stem diameter: 4.5 mm (0.18")</li> <li>Bulb draw: 1 mL</li> <li>Tip diameter: 0.9 mm (0.04")</li> </ul>
	Non-sterile	400 pcs/dispenser box	400	
134020-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	

5 mL capacity – extended tip – large bulb




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
134070	Non-sterile	250 pcs/dispenser box, 8 boxes/case	2000	<ul style="list-style-type: none"> <li>Capacity: 5 mL</li> <li>Total length: 153 mm (6.0")</li> <li>Drops/mL: 50</li> <li>Stem diameter: 4.6 mm (0.18")</li> <li>Bulb draw: 3.2 mL</li> <li>Tip diameter: 0.85 mm (0.03")</li> </ul>
	Non-sterile	250 pcs/dispenser box	250	
134070-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	
134070-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 20 bags/case	400	

5.8 mL capacity – standard




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
134050	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5.8 mL</li> <li>Total length: 147 mm (5.8")</li> <li>Drops/mL: 60</li> <li>Stem diameter: 4.6 mm (0.18")</li> <li>Bulb draw: 3.4 mL</li> <li>Tip diameter: 0.85 mm (0.03")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
134050-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	
134050-S20	Sterile	20 pcs/pack, 20 packs/case	400	

5.8 mL capacity – extended tip – standard




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
134060	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 5.8 mL</li> <li>Total length: 157 mm (6.2")</li> <li>Drops/mL: 50</li> <li>Stem diameter: 4.6 mm (0.18")</li> <li>Bulb draw: 3.4 mL</li> <li>Tip diameter: 0.85 mm (0.03")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
134060-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	

8.7 mL capacity – large bulb



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
134090	Non-sterile	400 pcs/dispenser box, 10 boxes/case	4000	<ul style="list-style-type: none"> <li>Capacity: 8.7 mL</li> <li>Total length: 147 mm (5.8")</li> <li>Drops/mL: 45</li> <li>Stem diameter: 6.1 mm (0.24")</li> <li>Bulb draw: 4.8 mL</li> <li>Tip diameter: 1.4 mm (0.06")</li> </ul>
	Non-sterile	400 pcs/dispenser box	400	
134090-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	
134090-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 20 bags/case	400	

## 7 mL capacity – graduated to 1.5 mL



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138002	Non-sterile Non-sterile	100 pcs/pack, 20 packs/case 100 pcs/pack	2000 100	<ul style="list-style-type: none"> <li>Capacity: 7 mL</li> <li>Drops/mL: 18</li> <li>Bulb draw: 4.8 mL</li> <li>Total length: 140 mm (5.5")</li> <li>Stem diameter: 8.0 mm (0.31")</li> <li>Tip diameter: 4.2 mm (0.17")</li> <li>Graduated up to: 1.5 mL</li> <li>Graduated increments: 0.5 mL</li> </ul>


## 15 mL capacity – graduated to 5 mL



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138005	Non-sterile Non-sterile	100 pcs/pack, 12 packs/case 100 pcs/pack	1200 100	<ul style="list-style-type: none"> <li>Capacity: 15 mL</li> <li>Drops/mL: 25</li> <li>Bulb draw: 5.8 mL</li> <li>Total length: 192 mm (7.6")</li> <li>Stem diameter: 10 mm (0.39")</li> <li>Tip diameter: 3.7 mm (0.15")</li> <li>Graduated up to: 5 mL</li> <li>Graduated increments: 1 mL</li> </ul>


# Extra-Long

## 6 mL capacity – 9 inch



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139030	Non-sterile Non-sterile	500 pcs/dispenser box, 10 boxes/case 500 pcs/dispenser box	5000 500	<ul style="list-style-type: none"> <li>Capacity: 6 mL</li> <li>Drops/mL: 25</li> <li>Bulb draw: 2.3 mL</li> <li>Total length: 225 mm (9")</li> <li>Stem diameter: 4.6 mm (0.18")</li> <li>Tip diameter: 2.4 mm (0.09")</li> </ul>
139038	Sterile	Individually wrapped, 100 pcs/box, 4 boxes/case	400	
139030-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 20 bags/case	400	


## 15 mL capacity – 8.5 inch



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139060	Non-sterile	250 pcs/dispenser box, 10 boxes/case 250 pcs/dispenser box	2500 250	<ul style="list-style-type: none"> <li>Capacity: 15 mL</li> <li>Drops/mL: 21</li> <li>Bulb draw: 5 mL</li> <li>Total length: 216 mm (8.5")</li> <li>Stem diameter: 7.6 mm (0.30")</li> <li>Tip diameter: 3.1 mm (0.13")</li> <li>Graduated up to: 5 mL</li> <li>Graduation increments: 1 mL</li> </ul>


**NEW!**

## 23 mL capacity – 12 inch




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
139050B	Non-sterile Non-sterile	100 pcs/dispenser box, 10 boxes/case 100 pcs/dispenser box	1000 100	<ul style="list-style-type: none"> <li>Capacity: 23 mL</li> <li>Drops/mL: 21</li> <li>Bulb draw: 10 mL</li> <li>Total length: 300 mm (12")</li> <li>Stem diameter: 8.5 mm (0.33")</li> <li>Tip diameter: 3.2 mm (0.13")</li> </ul>
139050-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/case	100	
139050-S20 <b>NEW!</b>	Sterile	20 pcs/bag, 5 bags/case	100	

## 0.8 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
136080	Non-sterile Non-sterile	500 pcs/dispenser box, 10 boxes/case 500 pcs/dispenser box	5000 500	<ul style="list-style-type: none"> <li>Capacity: 0.8 mL</li> <li>Drops/mL: 25</li> <li>Bulb draw: 0.2 mL</li> <li>Total length: 125 mm (4.9")</li> <li>Stem diameter: 3.6 mm (0.14")</li> <li>Tip diameter: 3.6 mm (0.14")</li> </ul>

## 1 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
136070	Non-sterile Non-sterile	500 pcs/dispenser box, 10 boxes/case 500 pcs/dispenser box	5000 500	<ul style="list-style-type: none"> <li>Capacity: 1.0 mL</li> <li>Drops/mL: 38</li> <li>Bulb draw: 0.2 mL</li> <li>Total length: 130 mm (5.1")</li> <li>Stem diameter: 3.8 mm (0.15")</li> <li>Tip diameter: 1.85 mm (0.07")</li> </ul>

## 1.2 mL capacity



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138040	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 1.2 mL</li> <li>Total length: 65 mm (2.56")</li> <li>Drops/mL: 25</li> <li>Stem diameter: 2.5 mm (0.1")</li> <li>Bulb draw: 0.9 mL</li> <li>Tip diameter: 2.5 mm (0.1")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138040-S01 <i>NEW!</i>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
138040-S20 <i>NEW!</i>	Sterile	20 pcs/bag, 25 bags/case	500	

## 1.3 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
134010	Non-sterile	500 pcs/dispenser box, 8 boxes/case	4000	<ul style="list-style-type: none"> <li>Capacity: 1.3 mL</li> <li>Total length: 51 mm (2.0")</li> <li>Drops/mL: 45</li> <li>Stem diameter: 1.15 mm (0.05")</li> <li>Bulb draw: 1 mL</li> <li>Tip diameter: 1.15 mm (0.05")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	

## 1.5 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
134020	Non-sterile	400 pcs/dispenser box, 8 boxes/case	3200	<ul style="list-style-type: none"> <li>Capacity: 1.5 mL</li> <li>Total length: 104 mm (4.1")</li> <li>Drops/mL: 50</li> <li>Stem diameter: 4.5 mm (0.18")</li> <li>Bulb draw: 1 mL</li> <li>Tip diameter: 0.9 mm (0.04")</li> </ul>
	Non-sterile	400 pcs/dispenser box	400	
134020-S01 <i>NEW!</i>	Sterile	Individually wrapped, 100 pcs/bag, 4 bags/case	400	

## 1.5 mL capacity




Catalog No.	Sterility	Packaging Information	Unit	Technical Data
136036	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 1.5 mL</li> <li>Total length: 116 mm (4.6")</li> <li>Drops/mL: 21</li> <li>Stem diameter: 3.2 mm (0.13")</li> <li>Bulb draw: 0.9 mL</li> <li>Tip diameter: 3.2 mm (0.13")</li> <li>Graduated up to: 0.3 mL</li> <li>Graduation increments: 0.1 mL</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
136036-S01 <i>NEW!</i>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
136036-S20 <i>NEW!</i>	Sterile	20 pcs/bag, 25 bags/case	500	

## 1.7 mL capacity



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
138020B	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 1.7 mL</li> <li>Total length: 87 mm (3.4")</li> <li>Drops/mL: 25</li> <li>Stem diameter: 4.5 mm (0.18")</li> <li>Bulb draw: 0.9 mL</li> <li>Tip diameter: 2.4 mm (0.09")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
138020-S01 <i>NEW!</i>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
138020-S20 <i>NEW!</i>	Sterile	20 pcs/bag, 25 bags/case	500	

## 4 mL capacity



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
136020	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>Capacity: 4 mL</li> <li>Total length: 85 mm (3.4")</li> <li>Drops/mL: 24</li> <li>Stem diameter: 2.5 mm (0.1")</li> <li>Bulb draw: 3 mL</li> <li>Tip diameter: 2.5 mm (0.1")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
136020-S01 <i>NEW!</i>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	
136020-S20 <i>NEW!</i>	Sterile	20 pcs/bag, 25 bags/case	500	

## Wide Bore Transfer Pipets

*For the rapid and effective transfer of viscous liquids and small particulates.*

These **wide bore transfer pipets** feature a wide tip opening designed specifically for the transfer of viscous liquids and small particulates. They are useful in the biofuel, petroleum, water treatment, food/beverage and pathology industries. The pipets are manufactured from low-density polyethylene (LDPE) and are packaged in convenient dispenser boxes; 500 pipets/box, 10 boxes/case.

**Ideal for transferring:**


- Algae
- Small tissue biopsies and pleural specimens
- Sludge, oil, slurry
- Plant specimens
- Sauces, gravies, syrup and condiments



## Wide Bore

Actual Size

7 mL capacity – large bulb, wide bore tip



Catalog No.	Sterility	Packaging Information	Unit	Technical Data
135040	Non-sterile	500 pcs/dispenser box, 10 boxes/case	5000	<ul style="list-style-type: none"> <li>• Total length: 125 mm (4.9")</li> <li>• Stem diameter: 7.9 mm (0.31")</li> <li>• Tip diameter: 5.5 mm (0.22")</li> </ul>
	Non-sterile	500 pcs/dispenser box	500	
135040-S01 <b>NEW!</b>	Sterile	Individually wrapped, 100 pcs/bag, 5 bags/case	500	



Producers of Exceptional Quality Lab Supplies

[www.globescientific.com](http://www.globescientific.com)

Globe Scientific Inc.

610 Winters Avenue • Paramus, New Jersey 07652 • USA

Customer service, sales and technical support:

Phone 1 (800) 394-4562 • 1 (201) 599-1400

Fax 1 (201) 599-1406

E-mail [mail@globescientific.com](mailto:mail@globescientific.com)

