

MEASURING WHEELS

MP401 METAL PROFESSIONAL SPOKED WHEELS

Our best selling metal wheel. The 4-foot circumference wheel levels out uneven ground by spanning divets that smaller wheels would dip into. The wheel's size enables it to roll and register feet clicks at the best pace in the industry.



ADVANCED COUNTER TECHNOLOGY

Our geared Mechanical Clicker Counter features easy-to-read numbers.

MP301

Not far behind the MP401 in popularity, this slightly more compact wheel is a little lower in price without compromising any durability.

MP301M

Our 1 meter circumference wheel registers a single meter click per revolution. It's about the same size as the MP301.

MP301DM

This is an industry first — we have 10 evenly spaced pins around the 1 meter circumference of this wheel. The result is a metal wheel that registers in decimeters.

MP401P

We mold 4-foot wheels for our RR series and for a less expensive alternative to the spoked wheels, we offer this model.



Limited lifetime warranty.

MODEL	UPC (052837)	UNITS	DIA.	CIRC.	SPECIAL FEATURES
MP301	026128	ft.	11-1/2 in.	3 ft.	Best seller!
MP301M	025763	m	.318 m	1 m	Steel metric wheel
MP301DM	026265	m, dm	.318 m	1 m	Most accurate decimeter wheel
MP401	025756	ft.	15-1/2 in.	4 ft.	Best seller!
MP401P	026128	ft.	15-1/2 in.	4 ft.	Plastic wheel, metal frame



MP Series Spoked Wheel Sell Sheet