

DYMO®

NEW

XTL™

Labels can be complicated so we made the labeller SIMPLE.

Introducing NEW DYMO® XTL™ 300 & XTL 500

The revolutionary label makers with life-like on screen preview and built-in label applications to simplify asset tracking, cable wraps and more.

LIFE-LIKE ON SCREEN PRINT PREVIEW - - - - -
Color display shows exactly how labels will look when applied to cables, pipes, panels and more




Patch Panel



Pipe Marking



Arc Flash



BUILT-IN LABEL APPLICATIONS

Simply select an application from the home screen to get started quickly

*when compared to creating labels on an XTL label maker without templates

PRE-LOADED LABEL TEMPLATES

Create labels 3x faster* and ensure perfect formatting to save time

TOUCH SCREEN

Helps make label creation easier and faster (available only on XTL 500)



Cables & Wires



Small Format Safety Signage



Asset Tracking & Barcodes


AVAILABLE THROUGH

GRAINGER®

FOR THE ONES WHO GET IT DONE

BUILT-IN LABEL APPLICATIONS

simply select an application from the Home screen to get started quickly



TOUCH SCREEN

helps make label creation easier and faster

(available only on XTL 500)



PRE-LOADED LABEL TEMPLATES

create labels 3x faster* and ensure perfect formatting to save time.

Also includes pre-set layouts for almost 100 patch panel models to eliminate size and spacing guesswork.



ADDITIONAL FEATURES INCLUDE:

- 1 3-Year Limited Warranty
- 2 Maximized print area helps reduce label waste
- 3 PC-connectivity to easily transfer labels to and from DYMO ID software for jobsite editing and printing
- 4 FREE DYMO ID software adds even more capability to your XTL label maker
- 5 Durable built-in cutter for fast label production
- 6 Impact-resistant rubber bumpers and wipe-clean keypad withstands harsh environments
- 7 On-screen label indicator automatically detects and displays the loaded label
- 8 Customizable printer settings eliminate unnecessary menus and steps


* when compared to creating labels on an XTL label maker without templates




DYMO® ID - ACHIEVING LABELING SIMPLICITY JUST GOT EASIER.

Using DYMO ID is easy thanks to a uniform experience that integrates the same great features found on your XTL™ label maker and packs them into a powerful PC-based software package. Once you've used an XTL label maker, learning to use DYMO ID will be a breeze. Available as a free download from dymo.com, DYMO ID will provide you with the functionality you need to tackle even the most complex labeling.

QUICKLY IMPORT DATA
to create a series of labels in just a few steps to eliminate manual entry, saving time and increasing productivity




OVER 200 PRE-LOADED SYMBOLS & IMAGES
or simply add a custom image to enhance communication and meet industry standards



Windows® is a registered trademark of Microsoft Corporation in the United States and other countries.

SHEET LABELS

Quickly print XTL label maker Laminated Wire/Cable Wrap sheet labels directly to a laser printer



QUICK CUSTOMIZATION & UPGRADES

Simply plug your XTL into a PC and use DYMO ID software to customize your preferences and keep it up to date

DYMO ID WORKS WITH THE FOLLOWING:

- XTL 300 Label Maker
- XTL 500 Label Maker
- XTL Laminated Wire/Cable Wrap Sheet Labels
- Works with Windows®7 and later



Available as a **FREE** download from www.dymo.com



XTL™

Selection Guide



	XTL™ 300	XTL™ 500
Item #	1868813 / Kit: 1868814	1868815
Printing System	Thermal Transfer	Thermal Transfer
Max Label Width	1"	2"
Labels Supported	DYMO XTL	DYMO XTL
Display	2.8" Color	4" Color Touch Screen
Print Speed (average)	1.25" in/sec	1.10" in/sec
Keyboard	QWERTY	QWERTY
Print DPI	300	300
Printable Lines	11	24
Barcodes Supported	Code 128 (Auto), Code 39, Code 39 Mod 43, EAN8, EAN13, UPC-A, Codabar, PDF-417, QR Code	Code 128 (Auto), Code 39, Code 39 Mod 43, EAN8, EAN13, UPC-A, Codabar, PDF-417, QR Code
Serialization	Yes	Yes
Cutter	Manual, Replaceable	Auto, Replaceable
Power Supply	Rechargeable Lithium Polymer Battery or AC Adapter	Rechargeable Lithium Polymer Battery or AC Adapter
Memory	41 MB	41 MB
Warranty	3-Year Limited	3-Year Limited
PC Connectivity	YES	YES
Software	DYMO ID, free download	DYMO ID, free download
Compatibility	Windows® 7 and later	Windows® 7 and later
Pack Contents	<ul style="list-style-type: none"> • DYMO XTL 300 Label Maker • AC Charging Adapter • USB Cable • Rechargeable Lithium Polymer Battery • (1) 1 in x 23 ft All-Purpose Vinyl, Black/White • Lanyard • Quick Start Guide • Software Download Card <p>Kit includes everything above, plus:</p> <ul style="list-style-type: none"> • Carrying Case • (1) 13/16 in x 1 9/16 in Laminated Wire/Cable Wrap, Black/White, 150 labels 	<ul style="list-style-type: none"> • DYMO XTL 500 Label Maker • Carrying Case • AC Charging Adapter • USB Cable • Rechargeable Lithium Polymer Battery • (1) 2 in x 23 ft All-Purpose Vinyl, Black/White • (1) 1 ½ in x 1 9/16 in Laminated Wire/Cable Wrap Black/White, 150 labels • Quick Start Guide • Software Download Card

LABEL APPLICATIONS		
110 & Terminal Blocks	✓	✓
Arc Flash	✓	✓
Asset Tracking	✓	✓
Breaker	✓	✓
Cable Wrap	✓	✓
Distribution Panel	✓	✓
Flag	✓	✓
General Label	✓	✓
Heat-Shrink Tube	✓	✓
Materials Management	✓	✓
Patch Panel	✓	✓
Pipe Marking	✓	✓
Quick Label	✓	✓
Safety	✓	✓

DYMO

XTL™

THE RIGHT LABEL



MORE VERSATILITY.

DELIVERING VERSATILITY AND DURABILITY, NO MATTER WHAT THE TASK.

DYMO XTL™ labels are durable and made for a variety of surfaces. Whether you are labeling to OSHA, ISO and ANSI color standards or labeling in harsh conditions, DYMO XTL labels have you covered. Jobsite-tested and UL-recognized, these labels won't smear or fade. Compatible with DYMO XTL label makers.



ONE LABEL SYSTEM. COUNTLESS APPLICATIONS.



RECOMMENDED APPLICATIONS:

DYMO XTL 300

- General Identification
- Barcodes (1D and 2D)
- Asset Tracking
- Wire and Cable Identification
- Networking Components Identification
- Facilities Identification

DYMO XTL 500

- General Identification
- Barcodes (1D and 2D)
- Asset Tracking
- Data Communications Identification
- MRO / Facilities Identification & Communication



XTL LABELS

Industrial-strength labels withstand the toughest conditions – moisture, chemicals, a wide range of temperatures, UV light and more.

- Durable thermal transfer printing technology – label text won't smear or fade
- Easy-to-peel split back design and pre-sized labels make applying labels quick and easy



ALL-PURPOSE VINYL

- Moisture, chemical and UV resistance makes vinyl ideal for indoor/outdoor use
- Wide range of colors that fit with OSHA, ANSI and ISO color standards to enhance workplace communication and safety
- UL recognized as a component to UL 969



FLEXIBLE CABLE WRAPS

- For labeling wires, cables and rounded surfaces, flexible nylon material is designed to conform and stick
- Tear-proof material resists damage when pulled through tight spaces or conduits
- UL recognized as a component to UL 969



LAMINATED WIRE/CABLE WRAPS

- Pre-sized wire/cable wraps with laminated overwrap protect printed areas from oil, chemicals, moisture, abrasion and fading
- Also available in sheet label formats for high-volume installations
- UL recognized as a component to UL 969



PRE-SIZED SAFETY LABELS

- Specific labels with colored headers including labels pre-printed with DANGER and NOTICE headers for on-demand printing of small format safety signage
- UL recognized as a component to UL 969



PERMANENT FLAT SURFACE

- For labeling panels, blocks, faceplates, shelves, bins, beams and more
- For labeling flat surfaces, a glossy finish leaves a professional look
- UL recognized as a component to UL 969



HEAT-SHRINK TUBES (CONTINUOUS AND PRE-SIZED)

- Heat-Shrink Tubes provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio
- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL-23053/5 (Class 1 & 3)
- UL recognized as a component to UL 224




PRE-SIZED LABELS

- Ideal for flat surface labeling like barcodes, faceplates, shelves, bins, beams and more
- Pre-Sized labels help facilitate batch label printing to improve productivity
- UL recognized as a component to UL 969



XTL LABELS: A VISUAL GUIDE


LABEL WIDTHS



ALL-PURPOSE VINYL COLORS



PRE-SIZED LABELS



PRE-SIZED SAFETY LABELS



1868715 / 2" x 4"




1868716 / 2" x 4"

PRE-SIZED HEAT-SHRINK TUBE



1868733 / 1" x 1 7/8" Black on White

LAMINATED WIRE/CABLE WRAPS




1868708 / 1-1/2" x 1-9/16"

PERMANENT FLAT SURFACE



1868736 / 3/8" Black on White



1868740 / 1/2" Black on Clear



THE RIGHT LABEL FOR THE RIGHT APPLICATION.

		All-Purpose Vinyl	Permanent Flat Surface	Flexible Cable Wrap	Heat-Shrink Tube (continuous & pre-sized)	Laminated Wire/Cable Wraps	Pre-Sized Labels	Pre-Sized Safety Labels
Surface	Flat	✓	✓	✓			✓	✓
	Wires & Cables	✓		✓	✓	✓		
	Curved	✓		✓				
	Flag	✓		✓				
	Textured	✓	✓	✓			✓	✓
Resistance	Heat/Cold	-40° to 140° F	-40° to 140° F	-40° to 140° F	Max 257° F	-40° to 140° F	-40° to 140° F	-40° to 140° F
	Outdoor	✓	✓				✓	✓
	UV Light	✓	✓	✓	✓	✓	✓	✓
	Oil	✓	✓		✓	✓	✓	
	Water	✓	✓		✓	✓	✓	✓
	Chemical	✓	✓		✓	✓	✓	
Industry Standards & Ratings	Color	OSHA, ANSI, ISO color standards						Colored headers to comply with OSHA, ANSI, ISO color standards
	UL Recognized as a component to	UL 969	UL 969	UL 969	UL 224	UL 969	UL 969	UL 969
	MIL-Spec & SAE				MIL-M-81531 MIL-STD-202G SAE-DTL-230535 (Class 1 & 3)			
	RoHS	✓	✓	✓	✓	✓	✓	✓






CONTINUOUS & PRE-SIZED LABELS




All-Purpose Vinyl



Flexible Cable Wrap



Permanent Flat Surface



Heat-Shrink Tube (continuous)

Text Color on Label Color	Length	1/4 in		3/8 in		1/2 in		3/4 in		1 in		1-1/2 in		2 in	
		Grainger	DYMO	Grainger	DYMO	Grainger	DYMO	Grainger	DYMO	Grainger	DYMO	Grainger	DYMO	Grainger	DYMO

ALL-PURPOSE VINYL

ABC	23 ft	-	-	-	-	40W064	1868741	40W065	1868742	40W066	1868743	40W067	1868744	40W068	1868745
ABC	23 ft	-	-	-	-	40W069	1868746	40W070	1868747	40W071	1868748	40W072	1868749	40W073	1868750
ABC	23 ft	-	-	-	-	40W074	1868751	40W075	1868752	40W076	1868753	40W077	1868754	40W078	1868755
ABC	23 ft	-	-	-	-	40W079	1868756	40W080	1868757	40W081	1868758	40W082	1868759	40W083	1868760
ABC	23 ft	-	-	-	-	40W084	1868761	40W085	1868762	40W086	1868763	40W087	1868764	40W088	1868765
ABC	23 ft	-	-	-	-	40W089	1868766	40W090	1868767	40W091	1868768	40W092	1868769	40W093	1868770
ABC	23 ft	-	-	-	-	40W094	1868771	40W095	1868772	40W096	1868773	40W097	1868774	40W098	1868775
ABC	23 ft	-	-	-	-	40W099	1868776	40W101	1868777	40W102	1868778	40W103	1868779	40W104	1868780
ABC	23 ft	-	-	-	-	40W105	1868781	40W106	1868782	40W107	1868783	40W108	1868784	40W109	1868785
ABC	23 ft	-	-	-	-	40W110	1868786	40W111	1868787	40W112	1868788	40W113	1868789	40W114	1868790
ABC	23 ft	-	-	-	-	40W115	1868791	40W116	1868792	40W117	1868793	40W118	1868794	40W119	1868795
ABC	23 ft	-	-	-	-	40W120	1868796	40W121	1868797	40W122	1868798	40W123	1868799	40W124	1868800
ABC	23 ft	-	-	-	-	40W125	1868801	40W126	1868802	40W127	1868803	40W128	1868804	40W129	1868805

PERMANENT FLAT SURFACE

ABC	29.8 ft	40W058	1868735	40W059	1868736	40W060	1868737	-	-	-	-	-	-	-	-
ABC	29.8 ft	40W061	1868738	40W062	1868739	40W063	1868740	-	-	-	-	-	-	-	-

FLEXIBLE CABLE WRAP

ABC	18 ft	-	-	-	-	40W130	1868806	40W131	1868807	40W132	1868808	-	-	-	-
-----	-------	---	---	---	---	--------	---------	--------	---------	--------	---------	---	---	---	---

HEAT-SHRINK TUBE (CONTINUOUS)

ABC	8.9 ft	40W133	1868809	-	-	40W134	1868810	-	-	40W135	1868811	-	-	-	-
-----	--------	--------	---------	---	---	--------	---------	---	---	--------	---------	---	---	---	---

*Tape length 5.9 ft for #1868812 only

For technical specifications on all DYMO XTL label types, please visit our website at www.dymo.com



Heat-Shrink Tube
(pre-sized)




Pre-Sized
Labels



Pre-Sized
Safety Labels



Laminated
Wire/Cable Wraps



Laminated Wire/Cable Wraps
(sheet labels)

Text Color on Label Color	Grainger	DYMO	Label Width	Label Length	Labels / Cartridge	Compatible Label Maker
---------------------------	----------	------	-------------	--------------	--------------------	------------------------

PRE-SIZED HEAT-SHRINK TUBE

ABC	40W050	1868717	1/4 in	1-5/16 in	81	XTL 500
ABC	40W051	1868718	1/2 in	1-5/16 in	65	XTL 500
ABC	40W052	1868719	1 in	1-5/16 in	60	XTL 500
ABC	40W053	1868720	2-1/8 in	1-5/16 in	25	XTL 500
ABC	40W054	1868731	1/4 in	1-7/8 in	81	XTL 500
ABC	40W055	1868732	1/2 in	1-7/8 in	65	XTL 500
ABC	40W056	1868733	1 in	1-7/8 in	60	XTL 500
ABC	40W057	1868734	2-1/8 in	1-7/8 in	25	XTL 500

PRE-SIZED LABELS

ABC	40W028	1868665	1/2 in	1/2 in	250	XTL 300, XTL 500
ABC	40W029	1868666	1/2 in	1 in	250	XTL 300, XTL 500
ABC	40W030	1868667	1/2 in	1-1/2 in	185	XTL 300, XTL 500
ABC	40W031	1868668	1 in	1 in	250	XTL 500
ABC	40W032	1868669	3/8 in	1 in	250	XTL 300, XTL 500
ABC	40W033	1868670	1/2 in	3/4 in	250	XTL 300, XTL 500
ABC	40W034	1868701	3/4 in	1 in	250	XTL 300, XTL 500
ABC	40W035	1868702	1 in	2 in	100	XTL 500
ABC	40W036	1868703	2 in	3 in	100	XTL 500

PRE-SIZED SAFETY LABELS (WITH COLORED HEADERS)

ABC	40W046	1868713	2 in	4 in	70	XTL 500
ABC	40W047	1868714	2 in	4 in	70	XTL 500
NOTICE ABC	40W048	1868715	2 in	4 in	70	XTL 500
▲ DANGER ABC	40W049	1868716	2 in	4 in	70	XTL 500

LAMINATED WIRE/CABLE WRAPS

ABC	40W037	1868704	13/16 in	13/16 in	250	XTL 300, XTL 500
ABC	40W038	1868705	13/16 in	1-9/16 in	150	XTL 300, XTL 500
ABC	40W039	1868706	13/16 in	4 in	75	XTL 300, XTL 500
ABC	40W040	1868707	1-1/2 in	13/16 in	250	XTL 500
ABC	40W041	1868708	1-1/2 in	1-9/16 in	150	XTL 500
ABC	40W042	1868709	1-1/2 in	4 in	75	XTL 500
ABC	40W043	1868710	2 in	13/16 in	250	XTL 500
ABC	40W044	1868711	2 in	1-9/16 in	100	XTL 500
ABC	40W045	1868712	2 in	4 in	70	XTL 500

LAMINATED WIRE/CABLE WRAPS (SHEET LABELS)

Text Color on Label Color	Grainger	DYMO	Label Width	Label Length	Labels/Sheet	Sheets/Pack	Labels/Pack
ABC	40W075	1908552	1 in	7/8 in	96	27	2592
ABC	40W076	1908553	1 in	1-5/8 in	48	53	2544
ABC	40W077	1908554	1 in	4 in	16	63	1008
ABC	40W078	1908555	1-1/2 in	7/8 in	60	34	2040
ABC	40W079	1908556	1-1/2 in	1-5/8 in	30	34	1020
ABC	40W080	1908557	2 in	7/8 in	36	28	1008
ABC	40W081	1908558	2 in	1-5/8 in	18	56	1008

Label your way to a **DYMO® XTL™** Printer

DYMO®

XTL™

BUY DYMO XTL LABELS
GET A DYMO XTL 300 KIT FREE



Part# 1868814 Grainger# 21HN25

GRAINGER 43DC75: Facility General Identification Bundle - Shelves, Bins, Panels, Switches

DYMO#	GRAINGER#	DESCRIPTION	QTY
1868814	21HN25	DYMO XTL 300 KIT	1
1868667	40W030	DYMO XTL 1/2" x 1-1/2" (12 mm x 38 mm) Pre-Sized Label, Black on White	2
1868701	40W034	DYMO XTL 3/4" x 1" (19 mm x 25 mm) Pre-Sized Label, Black on White	2
1868736	40W059	DYMO XTL 3/8" (9 mm) Permanent Flat Surface, Black on White	2
1868740	40W063	DYMO XTL 1/2" (12 mm) Permanent Flat Surface, Black on Clear	2
1868751	40W074	DYMO XTL 1/2" (12 mm) All-Purpose Vinyl, Black on White	6
1868753	40W076	DYMO XTL 1" (24 mm) All-Purpose Vinyl, Black on White	6

GRAINGER 43DC76: Cable and Wire Identification Bundle (Small Diameter) - Wires, Cables, Electrical Repairs

DYMO#	GRAINGER#	DESCRIPTION	QTY
1868814	21HN25	DYMO XTL 300 KIT	1
1868705	40W038	DYMO XTL 13/16" x 1-9/16" (21 mm x 39 mm) Laminated Wire/Cable Wrap, Black on White	2
1868735	40W058	DYMO XTL 1/4" (6 mm) Permanent Flat Surface, Black on White	3
1868736	40W059	DYMO XTL 3/8" (9 mm) Permanent Flat Surface, Black on White	3
1868806	40W130	DYMO XTL 1/2" (12 mm) Flexible Cable Wrap, Black on White	3
1868807	40W131	DYMO XTL 3/4" (19 mm) Flexible Cable Wrap, Black on White	3
1868809	40W133	DYMO XTL 1/4" (6 mm) Heat-Shrink Tube, Black on White	2
1868810	40W134	DYMO XTL 1/2" (12 mm) Heat-Shrink Tube, Black on White	2
1868811	40W135	DYMO XTL 1" (24 mm) Heat-Shrink Tube, Black on White	2



Wire & Cable Identification



Small Format Safety Signage



Pipe Marking

Offer valid June 1, 2016 to August 31, 2016 at participating Grainger locations. Quantities limited. Promotion available while supplies last.

Visit Grainger.com or your local branch for more details.

AVAILABLE THROUGH
GRAINGER®
 FOR THE ONES WHO GET IT DONE


Label your way to a **DYMO® XTL™** Printer

DYMO®

XTL™

BUY DYMO XTL LABELS

GET A DYMO XTL 500 KIT FREE



Part# 1868815 Grainger# 21HN26

GRAINGER 43DC77: Cable and Wire Identification Bundle (Large Diameter) - Wires, Cables & Electrical Repairs

DYMO#	GRAINGER#	DESCRIPTION	QTY
1868815	21HN26	DYMO XTL 500 KIT	1
1868702	40W035	DYMO XTL 1" x 2" (25 mm x 51 mm) Pre-Sized Label, Black on White	3
1868708	40W041	DYMO XTL 1-1/2" x 1-9/16" (38 mm x 39 mm) Laminated Wire/Cable Wrap, Black on White	3
1868717	40W050	DYMO XTL 1/4" x 1-5/16" (6 mm x 34 mm) Pre-Sized Heat-Shrink Tube, Black on White	3
1868718	40W051	DYMO XTL 1/2" x 1-5/16" (12 mm x 34 mm) Pre-Sized Heat-Shrink Tube, Black on White	3
1868719	40W052	DYMO XTL 1" x 1-5/16" (24 mm x 34 mm) Pre-Sized Heat-Shrink Tube, Black on White	3
1868720	40W053	DYMO XTL 2-1/8" x 1-5/16" (54 mm x 34 mm) Pre-Sized Heat-Shrink Tube, Black on White	3
1868736	40W059	DYMO XTL 3/8" (9 mm) Permanent Flat Surface, Black on White	6
1868751	40W074	DYMO XTL 1/2" (12 mm) All-Purpose Vinyl, Black on White	3
1868807	40W131	DYMO XTL 3/4" (19 mm) Flexible Cable Wrap, Black on White	3

GRAINGER 43DC78: Facility Safety & Asset Tracking Bundle - Facility, Asset & Inventory Management

DYMO#	GRAINGER#	DESCRIPTION	QTY
1868815	21HN26	DYMO XTL 500 KIT	1
1868667	40W030	DYMO XTL 1/2" x 1-1/2" (12 mm x 38 mm) Pre-Sized Label, Black on White	3
1868702	40W035	DYMO XTL 1" x 2" (25 mm x 51 mm) Pre-Sized Label, Black on White	3
1868703	40W036	DYMO XTL 2" x 3" (51 mm x 76 mm) Pre-Sized Label, Black on White	3
1868713	40W046	DYMO XTL 2" x 4" (51 mm x 102 mm) Pre-Sized Label, Black on White w/Orange Header	3
1868714	40W047	DYMO XTL 2" x 4" (51 mm x 102 mm) Pre-Sized Label, Black on White w/Yellow Header	3
1868715	40W048	DYMO XTL 2" x 4" (51 mm x 102 mm) Pre-Sized Label, Black on White w/Blue Header & Pre-Printed 'NOTICE'	3
1868716	40W049	DYMO XTL 2" x 4" (51 mm x 102 mm) Pre-Sized Label, Black on White w/Red Header & Pre-Printed 'DANGER'	3
1868751	40W074	DYMO XTL 1/2" (12 mm) All-Purpose Vinyl, Black on White	6
1868754	40W077	DYMO XTL 1-1/2" (41 mm) All-Purpose Vinyl, Black on White	3

GRAINGER 43DC79: Pipe & Hose Marking Bundle - Pipes, Valves, Hoses & Facility

DYMO#	GRAINGER#	DESCRIPTION	QTY
1868815	21HN26	DYMO XTL 500 KIT	1
1868720	40W053	DYMO XTL 2-1/8" x 1-5/16" (54 mm x 34 mm) Pre-Sized Heat-Shrink Tube, Black on White	3
1868750	40W073	DYMO XTL 2" (54 mm) All-Purpose Vinyl, Red on Clear	3
1868752	40W075	DYMO XTL 3/4" (19 mm) All-Purpose Vinyl, Black on White	3
1868753	40W076	DYMO XTL 1" (24 mm) All-Purpose Vinyl, Black on White	6
1868754	40W077	DYMO XTL 1-1/2" (41 mm) All-Purpose Vinyl, Black on White	3
1868755	40W078	DYMO XTL 2" (54 mm) All-Purpose Vinyl, Black on White	6
1868800	40W124	DYMO XTL 2" (54 mm) All-Purpose Vinyl, White on Black	3
1868805	40W129	DYMO XTL 2" (54 mm) All-Purpose Vinyl, Black on Grey	3