



RHC303012

by Wiegmann
Catalog ID: RHC303012

N3R Continuous Hinge Wall-Mount 30X30X12 Carbon Steel - Gray

Designed for use as wiring boxes and junction boxes. Provide protection in outdoor installations against rain, sleet, and snow, or indoors against dripping water.

- Bodies and doors fabricated from 14 gauge carbon steel. Continuous hinge. Hinge is made of galvanized steel with a stainless steel pin. No knockouts. Collar studs provided for mounting optional back panels. External mounting plates, top and bottom of enclosure. Hasp and staple provided for padlocking. Grounding provisions provided.

Product Details

General

| | |
|-----------------|---|
| Application | Designed for use as wiring boxes and junction boxes. Provides protection in outdoor installations against rain, sleet, and snow, or indoors against dripping water. |
| Color | Gray |
| Construction | Seam and Tack Welded |
| Cover Type | Hinged Cover |
| Finish Type | Smooth |
| Knockouts | No |
| Listings | UL, CSA |
| Material | Carbon Steel |
| Mounting Method | External Mounting Plates |
| Mounting Type | Wall Mount |
| Type | Enclosure |
| UPC | 786725406890 |

Dimensions

| | |
|----------------|-------------|
| Cubic Capacity | 10800 cu.in |
| Depth | 12 in |
| Height | 30 in |
| Weight | 96 lb |

| | |
|-------|-------|
| Width | 30 in |
|-------|-------|

Certifications and Compliance

| | |
|------------------|--|
| Certified Listed | <ul style="list-style-type: none">• UL• CSA |
| Nema Rating | NEMA 3R |
| UL Listed | Yes |