

RELIABILITY, PRECISION, SUPERIOR RESULTS

PROPERTY MANAGEMENT SOLUTIONS

PAINTER'S TAPES

You invest a considerable amount of resources into maintaining and restoring your property. And you understand that a simple coat of paint can make a difference in improving the attractiveness and increasing the occupancy rates of these spaces.

Shurtape offers an array of professional painter's tapes that are formulated to work on multiple surfaces and deliver the clean lines you expect, while removing cleanly and minimizing time-consuming touch-ups once the tape is removed.

FrogTape® brand painter's tape is the only painter's tape treated with PaintBlock® Technology, which reacts with latex paint to form a micro-barrier to instantly seal the edges of the tape. It is available in two different adhesive technologies – **FrogTape Multi-Surface**, featuring a medium adhesive ideal for cured paint, unfinished wood, metal, glass and more; and **FrogTape Delicate Surface**, with lower adhesion for use on wallpaper, faux finishes or paint that's only 24 hours old.

ShurRELEASE® Blue Painter's Tape is designed for masking cured painted walls, trim, woodwork, glass and metal to help protect surfaces and prevent paint bleed. This medium-adhesion painter's tape removes cleanly and easily for up to 14 days.

You already devote enough time, effort and money to property maintenance, so getting the job done right the first time matters. Shurtape offers a painting tape solution that will deliver reliability, precision and superior results with every paint job.





PAINTER'S TAPES



RELIABILITY, PRECISION, SUPERIOR RESULTS

PROPERTY MANAGEMENT SOLUTIONS

PAINTER'S TAPES

		Tensile	Adhesion to Stainless Steel	Thickness	Elongation
 <p>FrogTape® Multi-Surface Painter's Tape</p> <ul style="list-style-type: none"> • Medium adhesion for multiple surfaces • Leaves very sharp paint lines • For use on cured painted walls, wood trim, glass and metal • 21-day clean removal • UV-resistant up to 7 days 		22 lbs/in width	30 oz/in width	5.7 mils	10%
 <p>FrogTape® Delicate Surface Painter's Tape</p> <ul style="list-style-type: none"> • Low adhesion for delicate surfaces • Leaves very sharp paint lines • For use on fresh paint (24 hours), faux finishes and wallpaper • 60-day clean removal 		23 lbs/in width	14 oz/in width	3.6 mils	4.5%
 <p>ShurRELEASE® Blue Painter's Tape</p> <ul style="list-style-type: none"> • For masking cured painted walls, trim, woodwork, glass and metal • Medium adhesion • 14-day clean removal • UV-resistant 		24 lbs/in width	32 oz/in width	5.3 mils	8%

HEADQUARTERS & DISTRIBUTION CENTERS

US CORPORATE HEADQUARTERS
Shurtape Technologies, LLC
1712 8th Street Drive SE
Hickory, NC 28602 USA

NORTH CAROLINA
Catawba Industrial Place
3389 Catawba Industrial Place
Catawba, NC 28609

ARIZONA
First Commerce Center
725 N 73rd Avenue, Suite 112
Phoenix, AZ 85043

CANADA
6685 Kennedy Rd. Suite 3
Mississauga, ON
Canada L5T 3A5

tel: (888) 442-8273

tel: (828) 322-2700

tel: (800) 342-8273

tel: (800) 463-8273



SHURTAPE.COM
1.888.442.TAPE



Shurtape®
TRUE TO YOUR WORK™