





















Choose the right floor pad for the job.

Maintenance Operation	Equipment Speed	First Choice	Alternate Choices	
Stripping To remove finish, sealer and contaminants from the floor surface.	Rotary or Automatic	 3M™ High Productivity Pad 7300 Our most aggressive stripping pad. Unique open construction resists loading and clogging. For fast removal of finish and proven consistent stripping.	 3M™ Black Stripper Pad 7200 Standard of the industry. Consistent proven performance. Long pad life.	 3M™ Brown Stripper Pad 7100 Conformable stripping pad for uneven floors. Super heavy-duty scrubbing for 2-4 coat removal.
	Low Speed 175-600 RPM			
Scrubbing To provide a fresh new surface for finishing.	Rotary or Automatic	 Scotch-Brite™ Surface Preparation Pad Plus Long-lasting, high performance scrubbing pad for top coat removal prior to recoating.	 Scotch-Brite™ Surface Preparation Pad Heavy-duty scrubbing for top coat removal prior to recoating.	 3M™ Blue Cleaner Pad 5300 Heavy-duty scrubbing of floors.
	Low Speed 175-600 RPM			
Cleaning To remove light soil and other contaminants.	Rotary or Automatic	 Scotch-Brite™ Clean & Shine Pad 2-in-1 daily cleaning pad for low-speed scrubbers that gradually increases shine with repeated use.	 3M™ TopLine Autoscrubber Pad 5000 Scrubs and cleans. Open construction resists clogging. Ideal for autoscrubbers.	 3M™ Red Buffer Pad 5100 Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks.
	Low Speed 175-600 RPM			
Buffing To remove scuffs and black heel marks and enhance floor appearance.	Rotary	 3M™ White Super Polish Pad 4100 Ideal for removing soil and scuff marks with minimal dulling. Also used to polish wood floors.	 3M™ Red Buffer Pad 5100 Designed for everyday cleaning and light scrubbing to remove light soil, scuff marks and black heel marks.	
	Low Speed 175-600 RPM			
Burnishing To remove scuffs and marks, repair finish and improve gloss and image clarity.	Electric, Battery, Propane	 3M™ Eraser Burnish Pad 3600 Removes black marks and returns gloss in fewer passes than other pads while producing less dust. Ideal for harder finishes and high traffic areas. Excellent durability and minimal finish removal.	 3M™ Natural Blend Tan Pad 3500 Blend of natural and synthetic fibers. Ideal for harder finishes and high traffic conditions. Removes marks and scuffs while polishing.	 3M™ Tan Burnish Pad 3400 Produces good gloss improvement while removing scuffs and marks. Exceptional durability and life. Ideal for harder finishes and high traffic conditions.
	Ultra High Speed 1500 RPM & Above			
Best Gloss	Electric, Battery, Propane	 3M™ TopLine Speed Burnish Pad 3200 Optimizes UHS burnishing on a wide variety of finishes. Combines black mark removal and gloss generation in one pad.	 3M™ Natural Blend White Pad 3300 Blend of natural and synthetic fibers. Excellent results on a wide variety of finishes and traffic conditions. Consistent high gloss with minimal swirl marks.	
	Ultra High Speed 1500 RPM & Above			
Soft Finish	Electric, Battery, Propane	 3M™ Sky Blue Hi-Performance Burnish Pad 3050 Restores gloss to dull floors. Designed for frequent burnishing with less dust, point buildup and burning.	 3M™ Aqua Burnish Pad 3100 Good gloss improvement with exceptional durability and life. The soft finish problem solver.	
	Ultra High Speed 1500 RPM & Above			
Stone Floor Conditioning To clean and condition worn and dull stone floors.	Rotary, Automatic, Electric, Battery or Propane	 Scotch-Brite™ Sienna Diamond Floor Pad Plus Diamond-coated floor pads clean and condition worn and dull marble, terrazzo, slate and polished concrete, bringing it to a medium gloss.	<p>Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.</p> <p>Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.</p> <p>Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.</p>	
	Low to Ultra High Speed 175-1500 RPM & Above			
Stone Floor Polishing To clean and polish stone floors with medium shine in good condition.	Rotary, Automatic, Electric, Battery or Propane	 Scotch-Brite™ Purple Diamond Floor Pad Plus Diamond-coated floor pads further enhance the appearance of terrazzo, slate and polished concrete.		
	Low to Ultra High Speed 175-1500 RPM & Above			

Greener Solutions

The polyester fiber used to make a range of floor pads* contains a minimum of 50% post-consumer recycled content. The recycled polyester fiber used is third-party certified for post-consumer recycled content. *3M™ Brand Floor Pad families include: 3200, 3300, 3400, 3500, 3600, 5000 and 5100.