



**MCR**  
**SAFETY**

# N9690TC

## Ninja

### Cut Protection Specification Sheet

#### PRODUCT DESCRIPTION:

MCR Safety Ninja® gloves are engineered to provide the highest level of innovation. Each of the offerings in the Ninja® series include a unique shell and polymer combination incorporating the latest in hand protection technology. Our Ninja® Glove Line offers the greatest assortment of dexterity, sense of touch, and protection. The Ninja® Therma Force features a 13 gauge gray Dyneema®/Synthetic exterior with an acrylic terry interior liner. Black bi-polymer coated palm and fingertips.

#### FEATURES:

- Dyneema and Synthetic fibers for cut protection
- Excellent abrasion resistance
- Durable Bi-polymer coating
- Insulated with Acrylic Terry inner lining

#### APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Agriculture, Bottling, Carpentry, Construction, Demolition, Cold storage applications, Glass handling



#### TECHNICAL DATA FOR: N9690TC

<b>Series</b>	Ninja	<b>EN 388 : CE Score - Abrasion</b>	4
<b>Material Group</b>	Strings	<b>EN 388 : CE Score - Cut</b>	5
<b>Product Type</b>	Cut Protection	<b>EN 388 : CE Score - Tear</b>	4
<b>Glove Size</b>	Large	<b>EN 388 : CE Score - Puncture</b>	3
<b>Gauge</b>	13 / 7 Gauge	<b>ANSI Cut</b>	ANSI Cut A5
<b>Material</b>	Dyneema / Acrylic	<b>ANSI Puncture</b>	ANSI Puncture 4
<b>Insulated</b>	Insulated	<b>ANSI Abrasion</b>	ANSI Abrasion 4
<b>Lining</b>	Acrylic		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved




**MCR**  
SAFETY

# N9690TC

**Ninja**

**Cut Protection  
Specification Sheet**



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
N9690TCL	Large	10.228	5.629	N/A	33.192 lb.	0.461
N9690TCM	Medium	9.843	5.355	N/A	31.464 lb.	0.437
N9690TCS	Small	9.448	5.315	N/A	27.576 lb.	0.383
N9690TCXL	X - Large	11.024	5.827	N/A	36.144 lb.	0.502
N9690TCXXL	XX - Large	11.417	6.141	N/A	37.728 lb.	0.524

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved