




Is your facility synchronized?

Put everyone on the same page & promote productivity, reliability & efficiency with precisely synchronized time-keeping over multiple departments or work stations.

TimeTrax Sync™ Clock Starter Packs bundle together a synchronized clock starter system ideal for schools, small healthcare facilities, manufacturing areas, office settings, or phased projects. Easily expandable & extremely simple to install.



- Captures main time source using Network Time Protocol (NTP) Server, GPS, or Ethernet to ensure consistent, reliable time signal
- RF Wireless bundle uses dependable frequency-hopping technology to continuously broadcast time signal to unlimited number of clocks (analog or digital) up to 250,000 square feet of signal coverage
- Power over Ethernet bundle leverages convenient, cost-effective Ethernet infrastructure
- Available in analog or digital clock formats (5 clocks per pack) to meet the needs of any environment
- TTSync™ wall clocks search for time signal for consistently updated time
- Automatically adjusts for Daylight Saving Time & power outages for maintenance-free operation
- Flexible mounting options, including dual clock wall & ceiling brackets for enhanced viewing in long hallways & large open spaces. Wire guards & NEMA 4 clock covers also available
- Easily expandable by adding TTSync™ RF Wireless Transmitters (RF wireless bundle) or an unlimited number of clocks



Smart. scan QR code for industry solutions



LED & LCD Digital Bundles also available



TIMETRAX™ Sync

Synchronized Clock Starter Pack



STARTER PACKS

RF WIRELESS	5 Clocks (analog or digital), RF Wireless Transmitter, TimeTrax Sync™ Software
PART #	DESCRIPTION
WSCBA-5*	RF Wireless Analog Pack (12 Hour)
WSCBA-5D*	RF Wireless Analog Pack (12/24 Hour)
WSCBD-5	RF Wireless Digital Pack (4-digit, red LED)
WSCBLD-5*	RF Wireless Digital Pack (6 digit, LCD)
POWER OVER ETHERNET IP NETWORK	5 Clocks (analog or digital), TimeTrax Sync™ Software, RJ45 Cables
PART #	DESCRIPTION
SEBA5R3SR	PoE Analog Pack (12 Hour)
SEBD5R4SR	PoE Digital Pack (4-digit, red LED)
SEBD5R6SR	PoE Digital Pack (6-digit, red LED)

*Includes batteries

WARRANTY & GUARANTEE

Warranty	3-Year manufacturer's limited warranty
Guarantee	30-Day money back guarantee

ANALOG CLOCK SPECIFICATIONS

Time Update Frequency	RF WIRELESS Every 24 Hrs (2am)	PoE Continuous
Power Input	3.6 Volt Lithium Battery	48V DC Power over Ethernet IEEE.802.3af
Bezel Color	Black	
Weight	3.15lbs	
Clock Dimensions	13.25in Dia. x 2.5inD	
Mounting	Wall, Dual Wall, Dual Ceiling**	

**Brackets sold separately



DIGITAL CLOCK SPECIFICATIONS

FORMAT	LED RF WIRELESS	LCD RF WIRELESS	PoE IP NETWORK
Time Update Frequency	Every 20 Seconds	Every 24 Hours (2am)	Continuous
Power Input	105-240V AC	3.6V Lithium Battery	48V DC Power over Ethernet IEEE.802.3af
FORMAT	LED	LCD	
Visibility	250ft	75ft	
Digit Color	● Red	● Black	
Bezel Color	● Black		
CHARACTER HEIGHT/DIGITS	WEIGHT	DIMENSIONS (WXHxD)	
4in/4-digit HH:MM (LED & PoE)	2.15lbs	11.5in x 6.25in x 1.5in	
2.5in/6-digit HH:MM:SS (LCD)	1.45lbs	11.25in x 4.5in x 1.5in	
Mounting	Wall, Dual Wall, Dual Ceiling***		

***Brackets sold separately

ACCESSORIES

PART #	DESCRIPTION
S9A3AAGBxB	900MHz RF Wireless 13" Analog Clock-12 Hour Face
9D44BR	900MHz RF Wireless 4in x 4 Digit Red LED Digital Clock
S9D3L6LBxB	900MHz RF Wireless 2.5in x 6 Digit LCD Battery Operated Digital Clock
SED4RALDRB	PoE IP Network 4in x 4 Digit Red LED Digital Clock
42224	3.6 Volt Lithium Battery
42442	Dual 13in Analog/Digital Clock Wall Bracket
42321	4in x 4 digit & 2.5in x 6 digit Digital Dual Clock Wall Bracket
42443	Analog/Digital Dual Clock Ceiling Bracket
42314	13in Analog Clock Chrome Wire Guard
42400	4in x 4 digit Digital Clock Chrome Wire Guard
42690	13in Analog Clock NEMA 4 Cover
42689	Digital Clock NEMA 4 Cover

