


FEATURE FOCUS :: EZ-COIL EQUIPPED

SPRING DRIVEN WELDING REEL



STEEL CONSTRUCTION

High-Quality steel construction provides superior strength and durability for heavy-duty applications in commercial and industrial settings.

EZ-COIL EQUIPPED

A Coxreels patented safety system that retracts up to % S L O W E R than conventional reels

POWDER COAT

CPC[™] Powder Coat. Long lasting, chip resistant and rust inhibiting CPC[™] powder coat finish seals all steel components for maximum corrosion resistance.



1 EXTERNAL FLUID PATH

External fluid path with 90° full-flow dual ported brass swivel offering both connections from the same side of the reel. The swivel screws directly on 1" solid steel axle, for simple VITON® seal maintenance and fast and easy hose installation. No need to remove the reel from its mount.

- With swivel lock bracket ensures maximum safety.



7 1/4" STEEL BASE

Sturdy single pedestal design with solid one piece, heavy gauge ¼" steel base and support post, no weld, for maximum stability.



MOUNTING PATTERN

Simple slotted mounting pattern located in the steel base for fast and easy reel installation and detachment.



2 CARTRIDGE MOTOR

Lubricated and enclosed cartridge-style spring motor is easily removable for safe and convenient maintenance. Precision coil spring factory tuned and matched to application for longest life cycle and performance.



3 CNC SPUN DISCS

Heavy duty CNC robotically spun and ribbed discs with rolled edges for greater strength, durability, hose protection and operator safety.



4 PRECISION BEARINGS

Sturdy permanently lubricated precision bearings for smooth rotation and trouble-free operation.



5 LOCKING RING

Multi-position, robust zinc plated locking ring and non-corrosive stainless steel lock ratchet mechanism to secure hose at desired length.



6 SOLID STEEL AXLE

1" solid steel axle with flat arbor for strong spring engagement and stainless steel set screw for non-corrosive swivel assembly provides solid internal core, long lasting use and reliable performance. Not a hollow tube, no fluid travels through it.



8 SUPER HUBTM

Exclusive Super Hub[™] dual axle support system increases the stability during operation, reduces vibration and strengthens the structural integrity of the reel.



(9) MULTI-POSITION GUIDE ARM

Versatile steel guide arm adjusts to wall, floor, ceiling & vehicle mounting positions.



(10) FOUR-WAY ROLLER BRACKETS

Pinch-proof four-way rollers allow the hose to be pulled from 360° for greater directional use coverage.



11 HOSE STOP

Adjustable solid rubber hose stop for convenient lead length positioning.

ACCESSORIES & UPGRADES



Designed for

OXY-ACETYLENE
AND "T" GRADE FUEL



www.coxreels.com

800.COX.REEL P: 480.820.6396

F: 480.820.5132

E: info@coxreels.com