



ANTI-VIBRATION AIR GLOVE®

Utilizing Patented Air Glove Technology

Protects the palm, fingers and thumb from Impact and Vibration

- › Synthetic ultra suede leather provides excellent wear and flexibility
- › Silicone dots on the palm and fingertips ensure outstanding grip and flexibility
- › Mesh back allows ventilation and comfort
- › Durable Bubble Glove® bladder in the palm, fingers and thumb protects from vibration
- › Full finger style offers maximum protection
- › Neoprene cuff with hook and loop closure
- › Protects from vibration when using hand-held or hand guided power tools and machines such as sanders, grinders, disc cutters, hammer drills, brush cutters and mowers
- › Variations:
BGHIVIS - with high visibility fabrics

Model **BG408**



Meets ISO 10819:2013 & ANSI S2.73-2002 (R 2007)

The IMPACTO Air Glove reduces vibration energy transmission to the palm and fingers. Non-permeable polymer bladder with multiple individual air chambers provides effectiveness that won't degenerate. Soft, flexible bladder is designed to conform to the flex-lines of the palm and fingers helping to maintain tool control. The multiple air chambers construction of the Air Bladder ensures long lasting wear that won't bottom out. The Air Bladder helps prevent job specific impact and vibration hazards in the workplace. Full finger gloves are in conformance with International Anti-Vibration Glove Standard EN 10819:1996, Mechanical Vibration and Shock-Hand-Arm Vibration and North American Standard ANSI S2.73-2002 (R 2007) / ISO 10819.



EN 388:2016

Protective gloves against mechanical risks

EN 420:2003+A1:2009

General requirements for gloves

4 2 4 3 X

Sizing: Measure the circumference of the hand at the base of fingers.

Washing: Hand wash in cold water and soft detergent. Do not bleach, do not dry by machine, do not dry clean.

US Patents 7,865,969, D768,336. Canadian Patent 2,496,077. Other patents pending.

Part#	Glove	Hand	Circumference
BG40820	S	7	7" - 8" / 18-20 cm
BG40830	M	8	8" - 9" / 20-23 cm
BG40840	L	9	9" - 10" / 23-28 cm
BG40850	XL	10	10" - 11" / 28-33 cm
BG40860	XXL	11	11" + / 33 + cm

TRUSTED PROTECTION

ISO 9001:2015



IMPACTO.CA

N. America 888 232 0031

Free phone UK 0800 0280 243

T: 613 966 0062 F: 613 966 0067

PO BOX 524, BELLEVILLE, ON K8N 5B2

impacto@impacto.ca

Distributed by,

IMPACTO

PROTECTIVE PRODUCTS