





TACKLES BIG JOBS, EVEN IN SMALL SPACES.

XTRA SLIM JAWS ARE **40% THINNER** THAN A REGULAR WRENCH OF THE SAME SIZE. WHICH MEANS HARD-TO-REACH JOBS JUST GOT ABOUT **40% EASIER**.

Xtra Slim 3/16" jaws mean maximum accessibility.


The super wide opening lets you tackle big jobs with a compact wrench.

Our signature Code Blue® grips are designed for durability and comfort.




NEW XTRA SLIM JAW WRENCHES

Part #	A Overall Length		B Jaw Capacity		C Joint Thickness		D Joint Width		Weight	
	in.	mm.	in.	mm.	in.	mm.	in.	mm.	Pounds	Grams
6SWCB	6.93	176.02	1.34	34.00	0.55	13.97	2.56	65.02	0.44	199.58
8SWCB	8.49	215.65	1.50	38.10	0.55	13.97	2.87	72.90	0.74	335.20




ADJUSTABLE WRENCHES

CHANNELLOCK® Adjustable Wrenches have an endless number of uses. Strong, reliable and versatile — it's exactly what America has come to expect from CHANNELLOCK®.



JAW DESIGN



Longer jaws grip better, while thinner jaws give greater access in tight spaces.

ADJUSTABLE



4-thread knurl and non-protruding jaws provide greater capacity. Minimal head width improves performance in confined areas.

MEASUREMENT SCALES



Measurement scales (inches on front and millimeters on reverse) are handy for sizing nuts, pipe and tube diameters.

NEW XTRA SLIM JAW WIDE AZZ® CODE BLUE®

Model	Description	List
6SWCB	6" Adjustable Wrench	\$42.38
8SWCB	8" Adjustable Wrench	\$45.10

WIDE AZZ® CODE BLUE®

Model	Description	List
6WCB	6" Adjustable Wrench	\$36.28
8WCB	8" Adjustable Wrench	\$39.03

CHROME ADJUSTABLE WRENCHES

Model	Description	List
804	4" Adjustable Wrench	\$21.42
806W	6" Adjustable Wrench	\$22.79
808W	8" Adjustable Wrench	\$25.15
810W	10" Adjustable Wrench	\$30.60
812W	12" Adjustable Wrench	\$43.92
815	15" Adjustable Wrench	\$72.31
818	18" Adjustable Wrench	\$138.33
824	24" Adjustable Wrench	\$268.01
830	30" Adjustable Wrench	\$529.40

BLACK PHOSPHATE ADJUSTABLE WRENCHES

Model	Description	List
804N	4" Adjustable Wrench	\$19.80
806NW	6" Adjustable Wrench	\$21.69
808NW	8" Adjustable Wrench	\$23.82
810NW	10" Adjustable Wrench	\$29.62
812NW	12" Adjustable Wrench	\$42.25
815N	15" Adjustable Wrench	\$67.54
818N	18" Adjustable Wrench	\$135.09

CODE BLUE® ADJUSTABLE WRENCHES

Model	Description	List
806WCB	6" Adjustable Wrench	\$26.99
808WCB	8" Adjustable Wrench	\$31.46
810WCB	10" Adjustable Wrench	\$38.29
812WCB	12" Adjustable Wrench	\$53.35



©2015 CHANNELLOCK, INC., 1306 SOUTH MAIN ST., MEADVILLE, PA 16335 • P: 800-724-3018 F: 800-962-2583
ORDERS: orders@channellock.com • www.channellock.com