



Core & Coil (71A) HPS ~LT~ 200W

CORE & COIL HID HPS BAL 150W S55 QUAD KIT

The basic ballast is the open core and coil which is most often used as a component within a lighting luminaire. The core and coil also forms the nucleus of Philips Advance's five other ballast configurations.

Product data

General Information		Input Frequency	
ANSI Code	S55	Input Frequency	60 Hz
Lamp Type	150W HPS	Inp. Current (Open Circuit)	2.8/1.6/1.4/1.25 A
Number of Lamps	1 piece/unit	Input Current (Starting)	2/1.15/1/0.85 A
Circuit Type	HX-HPF	Input Current (Short Circuit)	1.15-1.75/0.65-1/0.55-0.85/0.5-0.75 A
Ballast Type	Magnetic HID	Secondary Short Circuit Current	3.95-4.85 A
Base Model	71A8172	Constant Wattage Deviation	Within Trapezoid
Core Size	3 X 4 (2 LW)	Ballast Factor (Nom)	1
Suitable For Outdoor Use	Yes	Power Factor (Nom)	0.90
Ignitor Catalog Number	LI551-H4	Nominal Open Circuit Voltage	120 V
Ignitor Temperature Rating	105°C	Input Current (Operating) (Nom)	1.65/0.95/0.83/0.72 A A
Capacitor Value	14 MFD	Input Power (Nom)	190 W
Capacitor Catalog Number	7C140M30RA	Rated Lamp Watts	150 W
Capacitor Requirements	280V	Wiring	
Capacitor Temperature Rating	105°C	Wire Striplength	0.5 mm
Capacitor Diameter/Oval Dimensions	1.65 in	Wire Length by Color	12"
Capacitor Height	2.75 in	Wire Type	Stranded
Automatic Restart	No	Remote Wiring Configuration Allowed	Yes
Operating and Electrical		Max Ballast-Lamp Distance Remote	2'
Input Voltage	120/208/240/277 V	Wiring	


Core & Coil (71A) HPS ~LT~ 200W

Recommended Fuse Value	10/5/5/4 A
Approval and Application	
Open Circuit Voltage Test (Volts)	110-130 V
Approbation Marks	ULR CSA certificate RoHS Compliant
Temperature Marking	E/E/E/E
UL Recognized	Yes
Hipot Test (1 Minute)	2000 V
Hipot Test (2 Seconds)	2500 V
UL Insulation Class	H(180°C)
UL Temperature Code	1029E

Product Data

Order product name	CORE & COIL HID HPS BAL 150W S55 QUAD KIT
EAN/UPC - Product	781087817216
Order code	71A8172001D
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	913700556509
Net Weight (Piece)	3.688 kg

Dimensional drawing



HPS BAL 150W S55 QUAD KIT

Product	C1	C2	A1	A2	B1	B2
CORE & COIL HID HPS BAL 150W S55 QUAD KIT	4.2 in	2.5 in	3.9 in	3.5 in	2.8 in	2.4 in

