


# Louvered Panel & Bin Combination Guide

for hanging bins and louvered panels manufactured by



AKROBINS®



- 2W072** (30210), **2W073** (30220)  
Each bin is 4.125 inches wide.  
Each row of bins uses two rows of louvers.
- 2RV98** (30224)  
Each bin is 5.5 inches wide.  
Each row of bins uses three rows of louvers.
- 2RV67** (30230), **2RV68** (30234)  
Each bin is 5.5 inches wide.  
Each row of bins uses three rows of louvers.
- 5W867** (30235)  
Each bin is 11 inches wide.  
Each row of bins uses three rows of louvers.
- 45MV65** (30237)  
Each bin is 6 inches wide.  
Each row of bins uses three rows of louvers.
- 30255** (2RV92)  
Each bin is 16.5 inches wide.  
Each row of bins uses three rows of louvers.
- 1UGP4** (30320)  
Each bin is 33 inches wide.  
Each row of bins uses three rows of louvers.
- 5W868** (30239), **2W779** (30240)  
Each bin is 8.25 inches wide.  
Each row of bins uses four rows of louvers.
- 2W076** (30250)  
Each bin is 16.5 inches wide.  
Each row of bins uses four rows of louvers.
- 2RV73** (30265)  
Each bin is 8.25 inches wide.  
Each row of bins uses five rows of louvers.
- 1UGP9** (30260)  
Each bin is 11 inches wide.  
Each row of bins uses six rows of louvers.
- 5YM95** (30270)  
Each bin is 16.5 inches wide.  
Each row of bins uses six rows of louvers.

Number of Louvers Per Panel			
Model Number	Width of Rows	Number of Rows	Number of Louvers/Row
1UMD7	16.5"	30	6
1UMD8	33"	30	12
3AJ36	16.5"	9	6
30632	31"	1	11
2W717	33"	9	12
1UME5	33"	36	12
4TJ79	33"	36 per side	12
40L708	49.5"	16	17
45MV85	16.5"	30 per side	6
1UME2	33"	30	12
1UME3	33"	30 per side	12
2W718	24.75"	10	9
1UMD9	33"	10	12




1UME5 with 5W875 AkroBins



45MV85 with 2RV92 AkroBins

INSIGHT®



- 6GDL3** (305A1), **6GDL5** (305A3), **6GDL7** (305A5)  
Each bin is 4.125 inches wide.  
Each row of bins uses two rows of louvers.
- 36GDL9** (305B1)  
Each bin is 5.5 inches wide.  
Each row of bins uses three rows of louvers.



1UMD9 with 54DE46, 54DE58 HSN Bins



2W717 with 2W074 AkroBins



3AJ36 with 1UGN3 AkroBins