





Capstone® Shield

ANSI 2021 CE EN166 CSA Z94.3 H2X ANTI-FOG 1/bag 36/case

- Fully adjustable elastic band.
 - Fits over prescription glasses.
 - Lens is coated to prevent fogging.
 - Soft vinyl goggle body conforms to facial contours.
 - Goggle provides protection against dust and chemical splash.
 - Scratch resistant polycarbonate lens provides 99% UVA/B/C protection.
 - Removable vent caps allow the user to remove when more ventilation is required or leave in place for unsurpassed chemical splash resistance.
-
- Goggle incorporated with removable shield provides full face protection.
 - 4 ventilation holes provide appropriate airflow.
 - Ratchet shield allows user to open or close in 3 positions for adjustment.
 - Polycarbonate shield conforms to the face offering increased impact and dust protection.



Part	Lens and Shield
GG504TSHIELD●●●●	 Clear H2X Anti-Fog Lens with Clear Shield
GG504DTSHIELD●●	 Clear H2X Anti-Fog Dual Lens with Clear Shield
GG504TSHIELDIR3●●●●	 IR3 H2X Anti-Fog Lens with Tinted* Shield
GG504TSHIELDIR5●●●●	 IR5 H2X Anti-Fog Lens with Tinted* Shield

*NOTE: Only the goggle for GG504TSHIELDIR3 and GG504TSHIELDIR5 contains IR dye. Due to the nature of the vented holes, the shield is only green tinted and does not contain the IR resin.



VPACK6

Pack of 6 clear disposable, tear-off visors, suitable for high dust or muddy working environments.

CAPSHIELD●●●

Ratcheting shield includes strap and clips allowing the user to add to either of the Capstone 500 Series goggles.



Capstone® 500 Series



- Fits over prescription glasses.
- Lens is coated to prevent fogging.
- Soft vinyl goggle body conforms to facial contours.
- Goggle provides protection against dust and chemical splash.
- Scratch resistant polycarbonate lens provides 99% UVA/B/C protection.
- Removable vent caps allow the user to remove when more ventilation is required or leave in place for unsurpassed chemical splash resistance.
- GG504T passes D3: Droplet & Splash Test – provides protection from droplets and splashes.



12/box 144/case

Gray Goggle with Quick Release Strap

Part Lens
GG504T ●●●●● Clear H2X Anti-Fog

Chemical Green Goggle with Neoprene Strap

Part Lens
GC504TN ●●●●● Clear H2X Anti-Fog

Capstone® Dual Lens



- Fully adjustable elastic band.
- Fits over prescription glasses.
- Lens is coated to prevent fogging.
- Dual pane lens consists of polycarbonate lens on the outer side with acetate anti-fog lens on inner side.
- Dual pane lens ensures ultimate anti-fog performance.
- Scratch resistant polycarbonate lens provides 99% UVA/B/C protection.
- Soft vinyl goggle body conforms to facial contours.
- Goggle provides protection against dust and chemical splash.
- Removable vent caps allow the user to remove when more ventilation is required or leave in place for unsurpassed chemical splash resistance.
- G504DT passes D3: Droplet & Splash Test – provides protection from droplets and splashes.



12/box 144/case

Gray Goggle with Quick Release Strap

Part Lens
G504DT ●●●●● Clear Dual Pane H2X Anti-Fog

There's more to see at
PyramexSafety.com

(P) 800.736.8673 | (F) 901.861.4967

Capstone® 600 Series



- Fits over prescription glasses.
- Indirect ventilation system prevents fogging.
- Includes interchangeable cloth and neoprene straps.
- Co-material goggle provides superior protection against dust entry and chemical splash.
- Thermoplastic (TPE) body with universal nose bridge is flexible and contours to the user's face.
- Passes D3: Droplet & Splash Test – provides protection from droplets and splashes.
- Passes D4: Dust Test – provides protection from dust particles.

1/box 72/case

Gray Goggle with Adjustable Strap

Part G604T2 • • • • • Lens Clear H2X Anti-Fog



Capstone® RL



- Lens is interchangeable.
- Fits over prescription glasses.
- Indirect ventilation system prevents fogging.
- Includes interchangeable cloth and neoprene straps.
- Co-material goggle provides superior protection against dust entry and chemical splash.
- Thermoplastic (TPE) body with universal nose bridge is flexible and contours to the user's face.
- G804TRL passes D3: Droplet & Splash Test – provides protection from droplets and splashes.

12/box 72/case

Gray Goggle with Adjustable Neoprene Strap

Part G804TRL • • • • • Lens Clear H2X Anti-Fog
 G824TRL • • • • • Gray H2X Anti-Fog



Part	Description
R8NEO	Replacement Neoprene Strap
R8CLO	Replacement Cloth Strap
R804T • • • • •	Replacement Clear H2X Anti-Fog Lens
R824T • • • • •	Replacement Gray H2X Anti-Fog Lens

There's more to see at
PyramexSafety.com

(P) 800.736.8673 | (F) 901.861.4967