

Hammers & Sledges

Item #	Description	UPC	Pack
		018371-	
ED61	3 LB DRILLING HAMMER W/FIBERGLASS & VINYL HANDLE, 10"	502627	4
ED7	4 LB DRILLING HAMMER W/FIBERGLASS HANDLE, 10"	502634	4
ED71	4 LB DRILLING HAMMER W/FIBERGLASS & VINYL HANDLE, 10"	502641	4
ED72	4 LB DRILLING HAMMER W/WOOD HANDLE, 10"	502658	4
ED8	4 LB BLACKSMITH HAMMER W/FIBERGLASS HANDLE, 16"	502665	4
ED9	4 LB ENGINEER HAMMER W/WOOD HANDLE, 16"	502672	4
S1	8 LB SLEDGE HAMMER W/HEAVY DUTY FIBERGLASS HANDLE, 32"	502689	1
S1A	8 LB SPLITTING MAUL W/FIBERGLASS HANDLE, 36"	502696	1
S2	6 LB DOUBLE FACE SLEDGE W/FIBERGLASS HANDLE, 34"	502702	1
S3	3 LB DOUBLE FACE SLEDGE W/FIBERGLASS HANDLE, 16"	502719	4
S31	2.5 LB DOUBLE FACE SLEDGE W/FIBERGLASS & VINYL HANDLE, 14"	502726	4
S4	8 LB DOUBLE FACE SLEDGE W/FIBERGLASS HANDLE, 34"	502733	1
S5	10 LB DOUBLE FACE SLEDGE W/FIBERGLASS HANDLE, 34"	502740	1

Replacement Handles

DASCO PRO fiberglass handles give your customers the toughness and durability they want for their striking tools. We pultrude up to 175 rovings of fiberglass per handle into a smooth, strong handle - many times tougher than wood. The waterproof, non-warping and non-corrosive features of fiberglass assures customer satisfaction. Each handle replacement kit comes with instructions, 2 part epoxy resin, stick and mixing cup.



Item #	Description	Length	UPC	Pack
881	36" SLEDGE-SPLITTING MAUL HANDLE	36"	000400	4
882	36" SINGLE BIT AXE HANDLE	36"	000417	4
884	36" PICK/MATTOCK HANDLE	36"	000431	4
885	36" AXE / SLEDGE / MAUL HANDLE	36"	000608	4
887	15" ENGINEER/BLACKSMITH HANDLE	15"	000622	4
888	36" DOUBLE BIT AXE HANDLE	36"	000639	4
700	EPOXY ADHESIVE A & B	GLUE	000394	EA

