


# SPLASH MOUNT FAUCETS – 8" O.C. – SWING SPOUTS KN54 • KL54 SERIES



1	KL54-Y001	FAUCET BODY ASSEMBLY
2	KL50-Y007	HOT VALVE ASSEMBLY – ¼ TURN – COMPRESSION
	KL50-Y007-CCV	HOT VALVE ASSEMBLY – ¼ TURN – CERAMIC
	KL50-Y007-KT	HOT VALVE ASSEMBLY – ¼ TURN – COMPRESSION – WITH HANDLE
	KL50-Y007CVKT	HOT VALVE ASSEMBLY – ¼ TURN – CERAMIC – WITH HANDLE
3	KL50-Y006	COLD VALVE ASSEMBLY – ¼ TURN – COMPRESSION
	KL50-Y006-CCV	COLD VALVE ASSEMBLY – ¼ TURN – CERAMIC
	KL50-Y006-KT	COLD VALVE ASSEMBLY – ¼ TURN – COMPRESSION – WITH HANDLE
	KL50-Y006CVKT	COLD VALVE ASSEMBLY – ¼ TURN – CERAMIC – WITH HANDLE
4	K50-0110	LEVER HANDLE REPLACEMENT KIT W/SCREW
	K50-0001	WRIST BLADE HANDLES, PAIR, 4"
	K50-0001-6	WRIST BLADE HANDLES, PAIR, 6"
5	KL40-1000	MOUNTING KIT
	KL40-2020	MOUNTING KIT, CLOSE ELBOWS
6	KL50-X132	STREAM REGULATOR SCREEN
7	KS11-12-X006	TUBULAR SWING SPOUT, S/S, 6"
	KS11-12-X008	TUBULAR SWING SPOUT, S/S, 8"
	KS11-12-X010	TUBULAR SWING SPOUT, S/S, 10"
	KS11-12-X012	TUBULAR SWING SPOUT, S/S, 12"
	KS11-12-X112	TUBULAR SWING SPOUT, S/S, 12" (FOR JOINTED APPLICATIONS ONLY)
	KS11-12-X014	TUBULAR SWING SPOUT, S/S, 14"
	KS11-12-X016	TUBULAR SWING SPOUT, S/S, 16"
	KS11-12-X018A	TUBULAR SWING SPOUT, S/S, 18"
	8	KN50-X120
KN50-X201		AERATOR 55/64 STREAM FEMALE 2.2 GPM VANDAL RESISTANT
KN50-X120-F		AERATOR 55/64 STREAM FEMALE 1.5 GPM ANTI-MICROBIAL
KN50-X201-F		AERATOR 55/64 LAMINAR FEMALE 1.5 GPM VANDAL RESISTANT ANTI-MICROBIAL
KN50-X120-A		AERATOR 55/64 STREAM FEMALE .5 GPM
KN50-X235-F		AERATOR 55/64 PC SPRAY FEMALE .35 GPM
KN50-X335-F		AERATOR 55/64 PC SPRAY .35 GPM FEMALE VANDAL RESISTANT
KN50-X201-A		AERATOR 55/64 PC SPRAY FEMALE .5 GPM VANDAL RESISTANT
KN50-X120-M		AERATOR 55/64 PC SPRAY FEMALE 1.0 GPM
KN50-X120S-06		AERATOR 55/64 ROSE SPRAY FEMALE 6.0 GPM
KN50-X203-F		AERATOR 15/16 LAMINAR FEMALE 1.5 GPM VANDAL RESISTANT ANTI-MICROBIAL
KN50-X203-A		AERATOR 15/16 PC SPRAY FEMALE .5 GPM VANDAL RESISTANT
KN50-X203		AERATOR 15/16 STREAM FEMALE 2.2 GPM VANDAL RESISTANT
KN50-X121		AERATOR 15/16 STREAM FEMALE 2.2 GPM
KN50-X121-F		AERATOR 15/16 STREAM FEMALE 2.2 GPM ANTI-MICROBIAL
KN50-X121-A		AERATOR 15/16 PC SPRAY FEMALE .5 GPM
KN50-X120-F		AERATOR 15/16 LAMINAR FEMALE 1.5 ANTI-MICROBIAL
KN50-X305-A		AERATOR 13/16-27 PC SPRAY FEMALE VANDAL RESISTANT