



- Category 6 Shielded Coupler
- Standard Hubbell Keystone Mounting
- True Gigabit Ethernet Performance
- RoHS Compliant

FEATURES

- Contacts: phosphorus bronze, gold-plating over nickel
- Performance: Category 6 Channel, 250MHz
- Material: Snap Fit connector body: tin and high-impact polymer
- Signal transmitted: 10/100/1000BASE-T
- Suppresses NEXT and AXT
- Simplifies moves, adds and changes (MACs)

SPECIFICATIONS

- Cable type:
 - Standard Category 6 shielded patch cables
 - RJ45 Female to RJ45 Female

STANDARDS

- TIA 568-C.2
- UL Listed 1863
- RoHS Compliant

HUBBELL iSTATION Category 6 Shielded Inline Coupler



Hubbell's Category 6 shielded inline couplers deliver reliable Category 6 channel performance to the work station, cross connect or to any AV installation. Simplifying adds, moves and changes, the Category 6 coupler allows easy plug-n-play style connections.

Requiring no 110 punch down, these connectors install with a snap into any Hubbell iSTATION product, module, frame, and Hubbell delivery system products, raceway and UDX panels.

Create a customized multimedia work station by snapping in a Category 6 shielded coupler along with a selection from HPW's extensive line of AV connectors, loaded modules, category rated jacks and fiber connectors.

APPLICATIONS

- 1000BASE-T Gigabit Ethernet, 100BASE-T, 10BASE-T, 155Mbps ATM
- AV devices, Analog video and Digital video



ORDERING INFORMATION

Category 6 Shielded Inline Coupler

Description	Type	Catalog Number
Category 6	Shielded	SFSC6



ACCESSORIES

USB 2.0 Full Speed 110 Extenders

Description	Color	Catalog Number
Module 1-U	Black	IMU1101BK
	Electric Ivory	IMU1101EI
	Gray	IMU1101GY
	Office White	IMU1101OW
	White	IMU1101W



Hubbell iSTATION Modular Face Plate Frames

	1-Gang	2-Gang
Office White	IMF1xx	IMF2xx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



Hubbell iSTATION Keystone Modules

Description	Catalog Number
Keystone, 2-port, flat, 1-unit	IM2K1xx

xx = Color: **AL** (Almond), **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



HDMI 110 Extender Modules

Description	Catalog Number
110 UTP 2-unit HDMI extender (pair)	IMH110ST2xx

xx = Color: **BK** (Black), **EI** (Electric Ivory), **GY** (Gray), **OW** (Office White), and **W** (White)



Hubbell iSTATION VGA and 3.5mm 110 Extender, 1.5-Unit

Color	Catalog Number
Black	IM15311015BK
Electric Ivory	IM15311015EI
Gray	IM15311015GY
Office White	IM15311015OW
White	IM15311015W



DIMENSIONS

