

Makita Air Compressor Part Breakdown - MODEL MAC700

Item	Description	Part #	Qty	Item	Description	Part #	Qty
1	Cylinder head	101001-E	1	37	Electric motor / Crankcase	251215-E	1
2	Valve seat to head gasket	211001-E	1	38	Exhaust valve seat	114001-E	1
3	Inlet valve seat	104001-E	1	39	Oil gauge gasket	217001-E	1
4	Inlet & Exhaust valve seat gasket	212001-E	1	40	Air tank	401129-E	1
5	Inlet & Exhaust valve plate	125001-E	2	41	Spring washer for motor cover	382004-E	4
6	Inlet & Exhaust spring plate	127001-E	2	42	Regulator	410030-E	1
7	Crankshaft bolt	352106-E	1	43	Rubber handle	435017-E	1
8	Valve plate screw	126001-E	4	44	Tank foot assembly	434002-E	4
9	Cylinder head bolt	352087-E	4	45	Quick coupler (1/4")	447013-E	1
10	Spring washer for head bolt	382011-E	4	46	Safety valve (1/4")	407001-E	1
11	Exhaust Elbow	151404-E	1	47	Drain cock	413008-E	1
12	Discharge tube assembly	230092S-E	1	48	Check valve	409004-E	1
13	Pressure gauge	411028-E	2	49	Power cord	452005-E	1
14	Unloading elbow	151001-E	1	50	Pressure switch	412024-E	1
15	Valve seat to cylinder gasket	213001-E	1	51	Regulator nipple	441001-E	1
16	Cylinder	201013-E	1	52	Unloading tube assembly (1/4")	240082-E	1
17	Piston	203002-E	1	53	Motor fan	431005-E	1
18	Compression ring	206002-E	2	54	Handle plug	439010-E	2
19	Oil control ring	207002-E	1	55	Air filter (element only)	171002-E	1
20	Piston pin	204002-E	1	56	Ring kit (#18 and 19)	RK700-E	1
21	Piston pin snap ring	205001-E	2	57	Valve kit (#5, 6, and 8)	VK700-E	1
22	Cylinder to crankcase gasket	214001-E	1	58	Gasket kit (#2, 4, 15 and 22)	GK700-E	1
23	Set nut (cylinder to crankcase)	371005-E	2	59	Plug for pr.switch manifold	360002-E	1
24	Spring washer (cyl to crankcase)	382005-E	2	69	Start Capacitor	460001-E	1
25	Double head screw	358001-E	2	71	Overload Switch	458001-E	1
27	Crankcase cover gasket	215001-E	1	72	Centrifugal Switch	459001-E	1
28	Crankshaft	302001-E	1		Compressor oil (1 quart)	181122-A	1
29	Crankcase cover	304013-E	1				
30	Connecting rod	316001-E	1				
31	Oil sight gauge	321001-E	1				
32	Oil draining plug	360001-E	1				
33	Motor cover	433011-E	1				
34	Motor / crankcase cover bolt	352071-E	9				
35	Air filter assembly	170006-E	1				
36	Oil filler/crankcase breather	324003-E	1				

