

Pin and Sleeve Devices/Mechanical Interlocks

Accessories

Closure Caps

Cap assemblies provide watertight sealing to a disconnected male IEC Pin and Sleeve plug or inlet. Manufactured of the same tough non-metallic material as the watertight IEC Pin and Sleeve devices for corrosion and abuse resistance.

Description	Catalog Number
Fits all 16 and 20A, 3 wire plugs and inlets.	PC320
Fits all 16 and 20A, 4 wire plugs and inlets.	PC420
Fits all 16 and 20A, 5 wire plugs and inlets.	PC520
Fits all 30 and 32A, 3 and 4 wire plugs and inlets.	PC3430
Fits all 30 and 32A, 5 wire plugs and inlets.	PC530
Fits all 60 and 63A plugs and inlets.	PC60
Fits all 100 and 125A plugs and inlets.	PC100



PC3430

Cover Assemblies

Replacement cover assemblies for use with watertight connector bodies and receptacles. Exact replacement cover assemblies required to maintain proper water ingress. They are not reverse compatible. Replacement covers are not interchangeable. Kit contains cover, arm assembly and installation tool.

Description	IP67	IP69k/4X
	Catalog Number	Catalog Number
Fits all 16 and 20A, 3 wire watertight female devices.	CA320	HBLCA320
Fits all 16 and 20A, 4 wire watertight female devices.	CA420	HBLCA420
Fits all 16 and 20A, 5 wire watertight female devices.	CA520	HBLCA520
Fits all 30 and 32A, 3 and 4 wire watertight female devices.	CA3430	HBLCA3430
Fits all 30 and 32A, 5 wire watertight female devices.	CA530	HBLCA530
Fits all 60 and 63A watertight female devices.	CA60	HBLCA60
Fits all 100 and 125A watertight female devices.	CA100	HBLCA100



CA60



HBLCA60

Cord Clamp and Locking Ring

Replacement cord clamp and locking ring for use with IEC plugs, connectors and inlets.

Description	Cord Clamp and Locking Ring	Locking Ring Only
	Fits all 16 and 20A, 3 wire plugs, connectors and inlets.	CC320
Fits all 16 and 20A, 4 wire plugs, connectors and inlets.	CC420	LR420*
Fits all 16 and 20A, 5 wire plugs, connectors and inlets.	CC520†	LR520*
Fits all 30 and 32A, 3 and 4 wire plugs, connectors and inlets.	CC3430	LR3430*
Fits all 30 and 32A, 5 wire plugs, connectors and inlets.	CC530†	LR530*
Fits all 60 and 63A plugs, connectors and inlets.	CC60	LR60*
Fits all 100 and 125A plugs, connectors and inlets.	CC100	LR100*

Note: *Locking Ring only for plugs and inlets.

†Consult factory.



CC3430



LR3430



SAB34



074093403

Liquidtight Adapters

Machined aluminum or non-metallic adapters are available to provide a means for attaching flexible liquidtight metal conduit to rear of a Hubbell Pin and Sleeve plug or connector. To install, remove cord grip and two gland cap screws. Use screws to attach adapter. Kellems® liquidtight conduit connectors are available to control arc of bend and to prevent conduit pull-out where vibration, motion or strain is present. These grips interface directly with Hubbell's liquidtight adapters and are available in a wide variety of NPT sizes and configurations. Consult your local code grounding requirements before using liquidtight adapters.

Rating of Hubbell Pin and Sleeve Device	Liquidtight Conduit Size	Liquidtight Adapters		Optional Kellems Liquidtight Conduit Grip
		Aluminum	Non-Metallic	
16 and 20 Amp 3 and 4 Wire	½" NPT	SA A12	—	074093402
	¾" NPT	SA A34	—	074093403
16 and 20 Amp 5 wire and 30 and 32 Amp 3 and 4 wire	½" NPT	SA B12	—	074093402
	¾" NPT	SA B34	—	074093403
	1" NPT	SA B100	—	074093404
	1¼" NPT	SA C125	—	074093405
30 and 32 Amp 5 wire and 60 and 63 Amp (all)	½" NPT	SA C12	SA C12NM	074093402
	¾" NPT	SA C34	SA C34NM	074093403
	1" NPT	SA C100	SA C100NM	074093404
	1¼" NPT	SA D125	—	074093405
100 and 125 Amp (all)	1¼" NPT	SA D125	—	074093405
	1½" NPT	SA D150	—	074093406