

MODEL NUMBER:

- 7385.050 Reliant 3 Single Control Centerset
Indexed Metal Lever Handle LESS drain & pop-up hole.
0.5 gpm Pressure Compensating Vandal Resistant Spray.

GENERAL DESCRIPTION:

All metal body with choice of Metal Lever, Indexed Metal Lever Handle or optional Extra Long Lever Handle. Washerless 47mm ceramic disc valve cartridge with integral hot limit safety stop. Durable cast brass waterway. Braided flexible supply hoses with 3/8" compression connectors. Pressure compensating vandal resistant spray with 0.5gpm/1.9L/min. maximum flow rate.

PRODUCT FEATURES:

Pressure Compensating Spray: Provides a constant water flow of 0.5 gpm throughout the pressure range.

Cast Brass Waterway with Flexible Supply Hoses: Strong and durable. Less potential for leaks.

Ceramic Disc Valve Cartridge: Assures smooth, precise valve control and a lifetime of drip-free, maintenance-free performance.

Adjustable Hot Limit Safety Stop: Limits the amount of hot water allowed to mix with cold. Reduces the risk of accidental scalding.

Lead Free: Faucet contains ≤ 0.25% total lead content by weighted average.

Simple One-Person Installation: Faucet drops in from top. Quick spin nuts secure faucet in place.


SUGGESTED SPECIFICATION

Single control lavatory fitting shall feature an all metal body with metal lever handle. Shall feature a cast brass waterway with flexible hose connections. Shall also feature a washerless ceramic disc valve cartridge with integral hot limit safety stop. Shall feature water conserving vandal resistant 0.5gpm/1.9L/min. pressure compensating spray. Fitting shall be American Standard Model # 7385.050. _____.

CODES AND STANDARDS

These products meet or exceed the following codes and standards:

- ANSI A117.1**
- ASME A112.18.1**
- CSA B 125.1**
- NSF 61/Section 9 and Annex G**



Product Number	Description	Finish Options	
		Polished Chrome	PVD Satin Nickel
		002	295
7385.050	Reliant 3 Single Control Centerset. Indexed (Red/Blue) Metal Lever Handle. Less drain, less pop-up hole. Pressure compensating vandal resistant 0.5 gpm spray.		

Meets the American Disabilities Act Guidelines and **ANSI A117.1** Requirements for the physically challenged.

7385.050

- Indexed (Red/Blue) metal lever handle
- Less drain, less pop-up hole

Available Modifications*			Part Suffix
Handle Options		Extra Long Handle	_LH