


# 24Y992 Digital Refrigerator / Freezer Thermometer

The 24Y992 is a low temperature digital thermometer designed to hang or stand within the food zone inside cold storage cabinets. This is one of the most accurate refrigerator / freezer instruments with a specification of  $\pm 1^{\circ}\text{F}$  ( $\pm 0.5^{\circ}\text{C}$ ), and is guaranteed accurate for life. The 24Y992 is  $^{\circ}\text{F}$  /  $^{\circ}\text{C}$  selectable with a minimum and maximum temperature feature. The unique ABS plastic frame design is removable for easy cleaning. Both the thermometer and the frame are water-resistant and incorporate an anti-microbial additive that prevents the growth of bacteria.

**ACTUAL SIZE**



## Specifications

- Temperature Range:  $-22^{\circ}$  to  $122^{\circ}\text{F}$  ( $-30^{\circ}$  to  $50^{\circ}\text{C}$ )
- Accuracy:  $\pm 1^{\circ}\text{F}$  ( $\pm 0.5^{\circ}\text{C}$ ) from  $-4^{\circ}$  to  $50^{\circ}\text{F}$  ( $-20^{\circ}$  to  $10^{\circ}\text{C}$ )  
 $\pm 1.8^{\circ}\text{F}$  ( $\pm 1^{\circ}\text{C}$ ) otherwise
- Resolution:  $0.1^{\circ}$
- Response Time: 60 second updates
- Water-resistant
- Min / Max and reset feature
- FDA-approved ABS plastic housing with anti-microbial additive
- Display:  $1.875'' \times .75''$  (48 mm x 19 mm)
- Battery Life: 300+ days, (1) 3V, CR2032 (included)
- Lifetime warranty (accurate for life)

LIFETIME WARRANTY INCLUDES CALIBRATION ACCURACY: Any AFL designated instrument which proves to measure temperatures out of the specified accuracy range, or be defective in material or workmanship, will be replaced without charge upon receipt of the unit prepaid.



## Packaging

- Individual Package Weight: 3 oz (85 g)
- Package Dimensions (L x W x H):  $5'' \times 1.75'' \times 7.25''$  (127 mm x 45 mm x 184 mm)
- Package Cube: 0.4
- Units per box (6) / Units per master carton (36)



Still straining to read those Bi-metal dial thermometers? Try our **NEW**, easy-to-read 24Y992 DIGITAL!



**Accuracy to the Highest Degree**  
Cooper-Atkins Corporation • 800-835-5011 • 860-347-2256 • www.cooper-atkins.com

AVAILABLE THROUGH  
**GRAINGER**  
FOR THE ONES WHO GET IT DONE

67-1291  
V0513