




On Target Every Time.

The all new **3600SS** sheds new light on perfectly aligned time card punches & document stamping with exclusive **Smart Site™** technology.



Part #3600SS

Customize It!
Date stamp &
up to 2 lines
of custom type.
MAR12 11:38AM
PYRAMID TIME SYS
888 479 7264

- Patent-pending Smart Site™ alignment guide ensures perfectly aligned time card punches & document stamping time after time
- Custom feature allows date stamp (DATE TIME AM/PM) with up to 2 lines of alphanumeric custom type for company name, address, URL or other custom info
- Counter mode enables sequential page numbering up to 9999 consecutive stamps
- Adjustable document edge side loading accommodates various paper sizes
- Equipped with 14 useful message selections for stamping time sensitive documents
- Adaptable right or left hand printing
- Capable of multi lingual printing, including English, Spanish & French

Smart Site™ Red LED alignment guide & bird's eye viewing window takes the guesswork out of time card punching & document stamping.

US PATENT #9,358,811 B1



STAMP



Smart.
scan QR code for
product info



3600ss : Corporate : Industrial : Healthcare : Food Service : Government

SPE (Savings Per Employee) : Average Annual Savings of \$928.20 per employee based on 7 minutes saved per day @ US Dept. of Labor 2012 Average Hourly Wage including Benefits.



3600SS

Smart Site™ Time Clock & Document Stamp




- Simple 2-minute set-up
- Displays time, date & day of week on easy to read, backlit LCD screen
- Prints date & time (AM/PM, Military, Military Hundredths, Military Tenths)
- Durable dot matrix printing ensures clear, easy-to-read punches time after time
- Long-lasting, easy replacement ribbon cartridge¹
- Care-free automatic reset for short months, leap year & daylight saving time
- Internal battery backup safeguards data & settings for up to 30 days without power
- Tamper-proof security lock helps protect against costly time theft

¹replace ribbon every 6 months for optimum performance

SPECIFICATIONS	
Size (WXHxD)	6.125in x 5.75in x 6.75in (15.55cm x 14.60cm x 17.2cm)
Weight	2.6lbs. (1.17kg)
Power	100-240VAC, 50/60Hz
Color	Black
Mounting	Wall or desktop
Warranty	1-year manufacturer's limited warranty

FEATURES	
Alignment	Smart Site™ Red LED guide
Custom Type	Date stamp & up to 2 lines alphanumeric custom type (up to 16 characters per line)
Counter Mode	Sequential numbering up to 9999
Loading	Side, adjustable document edge
Employee Capacity	Unlimited
Printing	Semi automatic or manual
Display	Time, date & day of week
Program Codes	AM/PM, Military, Military Hundredths, Military Tenths
Language Printing	English, Spanish, French



MESSAGE OPTIONS		
DATE TIME	DATE YR IN	DATE YR ORIG
DATE YR TIME	DATE YR OUT	DATE YR VOID
DATE YR APVD	DATE YR PAID	DATE YR USED
DATE YR FAXD	DATE YR RCVD	DATE YR CMPL
DATE YR FILE	DATE YR SENT	

ACCESSORIES	
PART #	DESCRIPTION
5000R	Replacement Ink Ribbon Cartridge
35100-10	Time Cards (100pk)
400-3	25 Capacity Adjustable Time Card Rack
400-X	25 Capacity Expandable Time Card Rack
300-1	Heavy Duty Metal Time Card Rack

- 3600SS Time Clock/ Document Stamp
- 25 Time Cards
- 2 Security Keys
- User Guide

