

# 5000+

Auto Totaling Time Clock

SIMPLE : SMART®



## Total Control of Payroll.

The **5000+ Auto Totaling Time Clock** is mathematically inclined with automatic employee time totaling for accurate, error-free payroll tracking. Tallies weekly, every 2 weeks, semi-monthly, or monthly pay periods for up to 100 employees.



Model 5000

- Automatically calculates worked time between punches & accumulates worked hours for weekly, every 2 weeks, semi-monthly or monthly pay periods
- Totals actual or rounded time, including none, 5, 10 & 15 minute rules for “clean calculations”
- Auto-align top loading time card feed saves time, eliminates card jams & enables single-hand operation
- Able to interface with TimeTrax™ Sync Bell Ringers and transmit time signal to TimeTrax™ Sync Analog and Digital Clocks
- Capable of multi-lingual printing, including English, Spanish & French



scan

Smart.  
scan QR code for  
product info



5000+ : Corporate : Industrial : Healthcare : Food Service : Government

SPE (Savings Per Employee) : Average Annual Savings of \$1,723 per employee based on 13 minutes saved per day @ US Dept. of Labor 2012 Average Hourly Wage including Benefits.

PYRAMID

# 5000+

## Auto Totaling Time Clock



- Simple 2-minute set-up
- Displays time, date & day of week on easy to read, backlit LCD screen
- Prints date & time (select AM/PM, Military, Military Hundredths, Military Tenths)
- Durable dot matrix printing ensures clear, easy-to-read punches time after time
- Long-lasting, easy replacement ribbon cartridge<sup>1</sup>
- Care-free automatic reset for short months, leap year & daylight saving time
- Internal battery backup safeguards data & settings for up to 30 days without power
- Tamper-proof security lock helps protects against costly time theft

<sup>1</sup>replace ribbon every 6 months for optimum performance

SPECIFICATIONS	
Size (WXHxD)	7in x 7.25in x 6.5in (17.8cm x 18.4cm x 16.5cm)
Weight	3.5lbs. (1.6kg)
Power	100-240VAC, 50/60Hz
Color	Black
Mounting	Wall or desktop
Warranty	1-year manufacturer's limited warranty

FEATURES	
Employee Capacity	100
Loading	Top
Program Codes	AM/PM, Military, Military Hundredths, Military Tenths
Display	Time, date & day of the week
Time Card Alignment	Automatic
Language Printing	English, Spanish, French
Auto Payroll Calculations	Weekly, every 2 weeks, bi-monthly or monthly
Rounding Rules	none, 5, 10 & 15 minute

ACCESSORIES	
PART #	DESCRIPTION
5000R	Replacement Ink Ribbon Cartridge
44100-10	Time Cards (100pk)
400-3	25 Capacity Adjustable Time Card Rack
400-X	25 Capacity Expandable Time Card Rack
300-1	Heavy Duty Metal Time Card Rack
5300	24Volt Bell Ringer Relay (1 zone)
41361	6in 24Volt Bell
41392	8in 24Volt Bell
5200	13in Analog Clock
DIG-4B	4in, 4-digit Red LED Digital Clock (stand alone)
41357G	4in, 4-digit Red LED Digital Clock

Model 5000

- 5000+ Auto Totaling Time Clock
- 25 Time Cards
- Ribbon
- 2 Security Keys
- User Guide

