

The thinnest butyl glove providing the best resistance to the most aggressive chemicals with dexterity and comfort

- The glove provides the best resistance to the most aggressive chemicals, without compromising dexterity or comfort.
- Flexible and excellent dexterity, designed for comfort with a natural, curved ergonomic shape and soft feel.



Industries

- Automotive
- Life Sciences
- Chemical

Applications

- Equipment repair & maintenance
- Loading and unloading of process equipment
- Handling incoming goods
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Charging and blending raw materials
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Cleaning furnaces, distillation pumps, valves or lines and crackers BTX process
- Unexpected leakages spills or other releases

Key Features

- 38-514 offers superior protection against aldehydes, ketones and esters as well as concentrated mineral acids
- The glove is very flexible and provides excellent dexterity
- Designed for comfort, with a natural, curved ergonomic shape and soft feel, they offer easy donning and good grip
- The absence of latex proteins means there's no risk of latex allergies
- Rough finish on the hand section of the glove for safer handling



Performance Standards



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 38-514	Butyl Polymer,	7, 8, 9, 10	350 mm, 14 inches	Black	• 36 pairs in a carton; individually wrapped with insert • Size 11 unavailable in Canada and USA

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Bld. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.