



Features:

- 800 lb. rated capacity
- Grip Strut tread
- Two 4" casters for easy transport; non-handrail models
- Step lock standard on handrail models
- Two 2.5" diameter pads for stability
- 1-1/16" tubular steel construction
- Complies with applicable OSHA & ANSI standards
- 50° safety angle incline
- Powder-coat gray finish
- Ship all-welded

WITH HANDRAILS							
<i>Serrated</i>							
Grainger Item #	Tri-Arc Model #	# of Steps	Step Width	Platform Height	Overall Height	Overall Length	Overall Width
24" W x 24" L Platform							
29RJ60	WLWP122424SL	2	24"	20"	56"	56"	35"
29RJ61	WLWP132424SL	3	24"	30"	66"	66"	35"
29RJ62	WLWP142424SL	4	24"	40"	76"	76"	35"
29RJ63	WLWP152424SL	5	24"	50"	86"	86"	35"
24" W x 35" L Platform							
29RJ64	WLWP122436SL	2	24"	20"	56"	46"	35"
29RJ65	WLWP132436SL	3	24"	30"	66"	54"	35"
29RJ66	WLWP142436SL	4	24"	40"	76"	62"	35"
29RJ67	WLWP152436SL	5	24"	50"	86"	71"	35"
24" W x 47" L Platform							
29RJ68	WLWP122448SL	2	24"	20"	56"	58"	35"
29RJ69	WLWP132448SL	3	24"	30"	66"	66"	35"
29RJ70	WLWP142448SL	4	24"	40"	76"	74"	35"
29RJ71	WLWP152448SL	5	24"	50"	86"	83"	35"
36" W x 35" L Platform							
29RJ72	WLWP123636SL	2	36"	20"	56"	46"	40"
29RJ73	WLWP133636SL	3	36"	30"	66"	54"	40"
29RJ74	WLWP143636SL	4	36"	40"	76"	62"	40"
29RJ75	WLWP153636SL	5	36"	50"	86"	71"	40"
36" W x 47" L Platform							
29RJ76	WLWP123648SL	2	36"	20"	56"	58"	40"
29RJ77	WLWP133648SL	3	36"	30"	66"	66"	40"
29RJ78	WLWP143648SL	4	36"	40"	76"	74"	40"
29RJ79	WLWP153648SL	5	36"	50"	86"	83"	40"

WITHOUT HANDRAILS							
<i>Serrated</i>							
Grainger Item #	Tri-Arc Model #	# of Steps	Step Width	Platform Height	Overall Height	Overall Length	Overall Width
24" W x 24" L Platform							
25NZ69	WLWP022424	2	24"	20"	20"	35"	28"
25NZ74	WLWP032424	3	24"	30"	30"	42"	28"
25NZ79	WLWP042424	4	24"	40"	40"	51"	28"
24" W x 35" L Platform							
25NZ70	WLWP022436	2	24"	20"	20"	46"	28"
25NZ75	WLWP032436	3	24"	30"	30"	53"	28"
25NZ80	WLWP042436	4	24"	40"	40"	62"	28"
24" W x 47" L Platform							
25NZ71	WLWP022448	2	24"	20"	20"	58"	28"
25NZ76	WLWP032448	3	24"	30"	30"	65"	28"
25NZ81	WLWP042448	4	24"	40"	40"	74"	28"
36" W x 35" L Platform							
25NZ72	WLWP023636	2	36"	20"	20"	46"	40"
25NZ77	WLWP033636	3	36"	30"	30"	53"	40"
25NZ82	WLWP043636	4	36"	40"	40"	62"	40"
36" W x 47" L Platform							
25NZ73	WLWP023648	2	36"	20"	20"	58"	40"
25NZ78	WLWP033648	3	36"	30"	30"	65"	40"
25NZ83	WLWP043648	4	36"	40"	40"	74"	40"

For more information, please contact your Grainger Representative or visit Grainger.com®