



Z812A4-XL

4" Centerset Gooseneck Faucet

TAG _____

Architectural/Engineering Specification:

Polished chrome-plated cast brass faucet body with integral shanks, quarter turn ceramic disc cartridges and a 3-1/2" [89mm] centerline rigid or swing gooseneck spout. Unit is furnished with a 2.2 GPM [8.3 L] pressure compensating aerator (complying with ANSI A112.18.1 Standard for flow), 4" [102mm] vandal-resistant color-coded metal wrist blade handles, mounting hardware and 1/2" NPSM coupling nuts for standard lavatory risers.

Zurn Lead Free products (-XL) is the line of durable, high quality brass faucets and fixtures that are designed and manufactured to comply with Section 1417 of the Safe Drinking Water Act (SDWA) which mandates the weighted average lead content of no more than 0.25% of the wetted surface.

Product Features:

- Heavy-duty quarter turn ceramic disc cartridge
- Low-lead compliant, chrome-plated cast brass body
- 3-1/2" gooseneck spout
- 4" color coded wrist blade handle
- 2.2 GPM aerator

Note: *This product should be used with a WaterSense labeled counterpart with a compatible flush volume to ensure that the entire system meets the requirements for water efficiency and performance.*

Compliance and Certification:

- ADA Compliant
- Zurn Lead Compliant



Aerator Options:

	Flow rate GPM [LpM]	Vandal Resistant	Pressure Compression	Outlet Type
-2F	2.2[8.3]	✓	✓	Aerator
-3F	0.5[1.9]	✓	✓	Spray
-4F	2.2[8.3]	✓	✓	Laminar
-7F	1.0[3.8]		✓	Spray
-16F	1.0[3.8]	✓	✓	Spray
-17F	1.5[5.7]	✓	✓	Aerator
-18F	1.5[5.7]	✓	✓	Laminar
-22F	1.0[3.8]	✓		Laminar
-25F	0.35[1.3]	✓	✓	Spray

Suffix Options:

- FC 2.0 GPM [7.6 L] Laminar Flow Control in Base of Spout
- FC _____ Plain end spout with Flow Control (Specify GPM Flow: 0.5, 1.0, 1.5)
- G 1-1/4" [32mm] Grid Strainer Drain
- P 1-1/4" [32mm] Pop-up Drain
- 140 Restricted 140° Swing Spout
- Other

Architectural/Engineering Approval

The information contained in this document is subject to change without notice. Please contact Zurn for most up to date information.





Z812A4-XL

4" Centerset Gooseneck Faucet

TAG _____

Rough-in dimensions/Overview dimensions

